

## VGA to HDMI Adapter with USB Audio & Power – Portable VGA to HDMI Converter – 1080p

**Product ID:** VGA2HDU



The VGA2HDU VGA to HDMI adapter lets you turn the VGA port on your Desktop or Laptop computer into an HDMI output port.

With the VGA2HDU, you can expand your VGA video output to accommodate the increasing number of displays and projectors that only support HDMI.

Not all VGA converters are created equal. This adapter ensures you're harnessing the highest video quality from your VGA output, with support for resolutions up to 1920x1080 (1080p).

For hassle-free setup the VGA to HDMI adapter allows for plug-and-play installation. Plus, with a built-in USB power cable the device is powered using the USB port on your computer. The VGA to HDMI adapter will work with any computer operating system, but when working with a Windows computer the adapter supports native USB audio, allowing you to add your computer audio to the HDMI signal.

The VGA2HDU is backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Connect your VGA-equipped computer to an HDMI home theatre system
- Share video content from your VGA-equipped computer on an HDMI television or projector

- Connect a legacy VGA-equipped device to a newer HDMI display
- Share audio from your Windows based PC

## Features

- Supports video resolutions up to 1920x1080
- Plug-and-play installation
- USB powered
- USB audio
- Compact, lightweight design

---

### Hardware

Warranty	2 Years
Active or Passive Adapter	Active
AV Input	VGA
AV Output	HDMI
Cabling	HDMI
Audio	Yes
Chipset ID	MacroSilicon - MS9282

---

### Performance

Maximum Analog Resolutions	1920x1080
Maximum Digital Resolutions	1920x1080
Supported Resolutions	1920x1080 (1080p) 1680x1050 (WSXGA+) 1600x1200 1600x900 1440x900 1400x1050 (SXGA+) 1366x768

1360x768  
 1280x1024  
 1280x960  
 1280x800  
 1280x768 (WXGA)  
 1280x720p (720p)  
 1280x600  
 1152x864  
 1024x768  
 800x600 (SVGA)  
 640x480 (480p)

Wide Screen Supported Yes

MTBF 1,063,669 hours

#### Connector(s)

Connector A	1 - VGA (15 pin, High Density D-Sub)
	1 - USB 2.0 Type-A (4 pin, 480Mbps)
Connector B	1 - HDMI (19 pin)

#### Special Notes / Requirements

Note	When used with a Windows computer this adapter supports native USB audio.
	If used with a computer, volume levels cannot be adjusted using the operating system. Volume levels can be controlled by the output device (TV, speakers, audio receiver, etc).

#### Power

Power Source	USB-Powered
--------------	-------------

#### Environmental

Operating Temperature	0C to 60C (32F to 140F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	40%-85%RH

**Physical  
Characteristics**

Color	Black
Material	Plastic
Product Length	9.8 in [25.0 cm]
Product Width	0.5 in [1.2 cm]
Product Height	3.1 in [7.8 cm]
Weight of Product	2.1 oz [60.0 g]

---

**Packaging  
Information**

Package Quantity	1
Package Length	5.0 in [12.7 cm]
Package Width	6.9 in [17.4 cm]
Package Height	0.9 in [2.3 cm]
Shipping (Package) Weight	3.3 oz [94.0 g]

---

**What's in the Box**

Included in Package	1 - VGA to HDMI adapter w/ USB power & audio
	1 - 2ft USB Extension Cable
	1 - Instruction Manual

---

**Warranty  
Information**

Warranty	2 Years
----------	---------

---

*\*Product appearance and specifications are subject to change without notice.*

