

1ft (30cm) Heavy Duty Power Cord, Twist-Lock NEMA L5-15P to NEMA 5-15R Black Adapter Cord, 15A 125V, 14AWG, Heavy Gauge Plug Converter Cable, TAA Compliant, UL Listed

Product ID: W31C-4100-POWER-CORD



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Certifications, Reports and Compatibility



Applications

- Heavy Duty power cord supports high-powered equipment and PDUs
- Extend a server or rackmount equipment power cord by an additional 2ft

Features

- **HEAVY DUTY ADAPTER CABLE:** 1ft (30cm) Adapter Power Cable with Twist-Lock NEMA L5-15P to NEMA 5-15R connector works with servers or high-power equipment; Locking L5-15 plug securely attaches to an outlet or power source; Indoor use; Rated up to 125V at 20A
- **BUILT FOR PERFORMANCE AND SAFETY:** UL Listed; VW-1 Fire Rated cable with fully molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- **SPECS:** 1ft (30cm); TAA Compliant; Twist-Lock NEMA L5-15P to NEMA 5-15R; 14AWG; 125V 15A (Max); Jacket Rating: SJT; Color: Black; Temperature Range: -4F to 221F (-20 to 105); Cable O.D.: 0.36in (9.3mm)
- **COMPATIBILITY:** NEMA L5-15P to NEMA 5-15R power cord works with North American PDUs and high-powered devices; Convert a NEMA L5-15 outlet to 5-15R for convenient integration with servers, switches, or UPS; Heavy duty adapter power cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, the heavy duty adapter power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This adapter power cable is available in other plug configurations

Hardware

Warranty	Lifetime
Number of Conductors	3
Connector Plating	Nickel
Cable Jacket Material	PVC
Fire Rating	VW-1 Rated
Cable Type	SJT

Performance

Maximum Cable Length	1.0 ft [0.3 m]
----------------------	----------------

Connector(s)

Connector A 1 - NEMA L5-20P (North America)

Connector B 1 - NEMA 5-15 Power (North America)

Power

Output Current 15A

Environmental

Operating Temperature -20 to 105C (-4 to 221F)

Storage Temperature -20 to 105C (-4 to 221F)

Humidity 0% to 65% RH

Physical Characteristics

Color Black

Wire Gauge 14 AWG

Cable Length 1.0 ft [0.3 m]

Cable OD 0.4 in [9.3 mm]

Product Length 12.0 in [30.5 cm]

Product Width 1.5 in [3.9 cm]

Product Height 1.5 in [3.9 cm]

Weight of Product 5.7 oz [162.0 g]

Packaging Information

Package Length 6.9 in [17.4 cm]

Package Width 5.7 in [14.5 cm]

Package Height 1.7 in [4.2 cm]

Shipping (Package) Weight 6.2 oz [176.0 g]

What's in the Box

Included in Package 1 - 1ft NEMA 5-15R to NEMA L5-15P Heavy-Duty Power Cord

Warranty Information

Warranty

Lifetime

**Product appearance and specifications are subject to change without notice.*

