


4U Hinged Wall Mount Patch Panel Bracket - 6 inch Deep - 19" Patch Panel Swing Rack for Shallow Network Equipment- 33lbs

Product ID: WALLMOUNTH4



The WALLMOUNTH4 4U 19in Hinged Wall Mounting Bracket for Patch Panels is 6in deep and sturdily designed to provide a dependable solution for mounting a patch panel, or other slim 19in networking equipment to a wall.

The patch panel wall mount features a hinged design for easy access to configuration buttons, ports and cables. The wall mounting holes are spaced 16 in. apart, making it suitable for mounting on almost any wall, based on common wall-frame stud spacing.

Backed by a StarTech.com 2-year warranty.

Certifications, Reports and Compatibility



Applications

- Wall mount patch panels and other slim 19" rackmount equipment

Features

- **EASY EQUIPMENT ACCESS:** The patch panel wall mount features a hinged design for easy access to configuration buttons, ports and cables, and to the rear of the mounted equipment for easy adjustment
- **STURDY CONSTRUCTION:** Made of sturdy cold rolled steel, this patch panel swing bracket is designed to provide

a dependable solution for mounting slim 19in networking equipment to a wall

- **STANDARDIZED HOLE SIZING:** The 4U hinged wall mount patch panel bracket is positioned 16in apart, exactly matching standard drywall construction framework to ensure simple and secure wall-stud anchoring
- **OPTIMIZED WORKSPACE:** This durable 4U hinged wall mount patch panel bracket has a maximum mounting depth of 5.8in [14.8cm] and a maximum weight capacity of 33.2lb [15kg]
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this patch panel bracket is backed for 2-years, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	2 Years
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Open Frame
U Height	4U
Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity	33.1 lb [15 kg]
-----------------	-----------------

Physical Characteristics

Color	Black
Construction Material	Steel

Product Measurements

Product Length	6.0 in [15.2 cm]
Product Width	6.0 in [15.2 cm]
Product Height	6.8 in [17.2 cm]
Weight of Product	4.9 lb [2.2 kg]
Maximum Mounting Depth	5.8 in [14.8 cm]

Packaging Information

Flat Pack (Assembly Required)	No
Package Length	7.5 in [19.0 cm]
Package Width	20.8 in [52.8 cm]
Package Height	8.9 in [22.6 cm]
Shipping (Package) Weight	7.8 lb [3.5 kg]

What's in the Box

Included in Package	1 - Wall-Mount Rack
	4 - M6 Screws
	4 - M6 Cage Nuts
	4 - Plastic Washers
	4 - Wall Screws
	4 - Plastic Anchors

Warranty Information

Warranty	2 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*

