



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

[Customer Drawing](#)

Nb of contacts Thermocouple	1
Wire Size/AWG	24 - 20
Size	0B
Suggested matching part	FGG.0B.560.ZZF
Series	B - Indoor keyed

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/egg-0b-660-zzf.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Nb of contacts Thermocouple	1
Contact Termination Thermocouple	Crimp
Bucket Dia.	1.1
Contact Dia.	0.9
Wire Size/AWG	24 - 20

Form & Material

Shell style / Model id	EG - Type K thermocouple female crimp contact, standard barrel
Housing material	Thermocouple / Alumel
Keying	No keying
Weight	0.18 g

Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	No IP rating
Endurance	1000 mating cycles
Temperature range	-55°C / +250°C (max. temperature valid for short periods of use.)

Recommended By Lemo

Tools

Positionner	DCE.91.090.BVM
Extraction tool	DCC.09.05B.LAG
Crimp tool	DPC.91.701.V

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/egg-0b-660-zzf.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.