



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[Catalog](#)

[Customer Drawing](#)

Jacket cable outside diameter [mm]	6.30 - 7.20 mm
------------------------------------	----------------

Size	1B
------	----

Series	B - Indoor keyed
--------	------------------

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/fgg-1b-772-dn.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-1b-772-dn.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Form & Material

Shell style / Model id	FG - B series cable collet
Housing material	Brass (nickel plated [SAE AMS QQ N 290]) collet
Keying	No keying
Weight	0.86 g

## Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP50
Endurance	N/A
Temperature range	-55°C / +250°C (max. temperature valid for short periods of use.)
Salt Spray Corrosion	>1000 hr

## Cable fixation

Fixation type	Cable collet
Jacket cable outside diameter [mm]	6.30 - 7.20 mm

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/fgg-1b-772-dn.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-1b-772-dn.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.