



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

[See video assembly instructions](#)

Number of contacts Low Voltage	12
Wire Size/AWG	26 - 22
Gender	Standard
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	5.30 - 14.00 mm
Size	2F
Series	F - Rugged Push-Pull

https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/fgn-2f-312-clc.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Number of contacts Low Voltage	12
Contact Termination Low voltage	Crimp
R (max)	6.1 mOhm
Insert configuration value	2F.312 - 12 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	7 A
Vtest (contact-contact)	1650 V (AC), 2350 V (DC)
Vtest (contact-shell)	2000 V (AC), 2850 V (DC)
Contact retention	22 N
Max. Conductor	0.34 mm ² (AWG 22)
Min. Conductor	0.14 mm ² (AWG 26)
Bucket Dia.	0.8 mm (0.031in)
Contact Dia.	0.7 mm (0.028in)
Wire Size/AWG	26 - 22
Gender	Standard

Form & Material

Shell style / Model id	FG - Straight plug
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and nut, other pieces brass
Locking system	Push-pull
Keying	3 keys (beta=165, gamma=30, plug: male contacts, receptacle: female contacts)
Weight	16.8 g

https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/fgn-2f-312-clc.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


Environment

Technical domain	Motorsport, Security and Defence
Environmental sealing (IP rating)	IP67
Endurance	5000 mating cycles
Temperature range	-55°C / +200°C (max. temperature valid for short periods of use.)
Climatical Category	50/175/21 (Aluminium shell)
Humidity (max)	<=95% [at 60 deg C /140 F]
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

Cable fixation

Cable termination protection	Heatshrink
Fixation type	Heatshrink
Jacket cable outside diameter [mm]	5.30 - 14.00 mm

Drawings



Dimensions

	M	A	B	L	X
mm.	17.9	17	14	27.8	8
in.	0.7	0.67	0.55	1.09	0.31

https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/fgn-2f-312-clc.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Recommended By Lemo

Accessories

Replacement contact	FGG.0B.555.ZZC
Compatible cap	BFG.2F.100.XAZ

Tools

Positionner	DCE.91.070.BVC
Extraction tool	DCF.93.070.4LT
Crimp tool	DPC.91.701.V

Cables

Cable PartNumber	Material	Colour	Cable image
CMN.12.T22.070QGZE	TPR (medical)	Grey	
CMN.12.T28.054PGZE		grey	
CMN.12.T28.054PNZE			
112240	PTFE	White	
112260	PTFE	White	
112280	PVC	Black	
124080	PVC	Grey	
124084	PVC	Black	
212220	PVC	Black	
212240	PVC	Black	
212250	PVC	Grey	
212260	PVC	Black	

https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/fgn-2f-312-clc.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.