



Image for illustrative purpose only

## Summary

[Request a quote](#)

[Catalog](#)

[See video assembly instructions](#)

|                                    |                                                                  |
|------------------------------------|------------------------------------------------------------------|
| Number of contacts Low Voltage     | 19                                                               |
| Wire Size/AWG                      | 26 - 22                                                          |
| Gender                             | Standard                                                         |
| Plug                               | Plug - Straight                                                  |
| Locking system                     | Push-pull                                                        |
| Jacket cable outside diameter [mm] | 5.30 - 14.00 mm                                                  |
| Size                               | 2F                                                               |
| Suggested matching part            | <a href="#">EGN.2F.319.CLM</a><br><a href="#">PHN.2F.319.CLM</a> |
| Series                             | F - Rugged Push-Pull                                             |

[https://www.lemo.com/int\\_en/solutions/optima/f-rugged-push-pull/fgn-2f-319-clc.html](https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/fgn-2f-319-clc.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

|                                 |                               |
|---------------------------------|-------------------------------|
| Number of contacts Low Voltage  | 19                            |
| Contact Termination Low voltage | Crimp                         |
| R (max)                         | 6.1 mOhm                      |
| Insert configuration value      | 2F.319 - 19 Low Voltage       |
| Insulator                       | L: PEEK (UL 94 / V-0/1.5)     |
| Rated current                   | 5 A                           |
| Vtest (contact-contact)         | 1550 V (AC), 2200 V (DC)      |
| Vtest (contact-shell)           | 1650 V (AC), 2350 V (DC)      |
| Contact retention               | 22 N                          |
| Max. Conductor                  | 0.34 mm <sup>2</sup> (AWG 22) |
| Min. Conductor                  | 0.14 mm <sup>2</sup> (AWG 26) |
| Bucket Dia.                     | 0.8 mm (0.031in)              |
| Contact Dia.                    | 0.7 mm (0.028in)              |
| Wire Size/AWG                   | 26 - 22                       |
| Gender                          | Standard                      |

## Form & Material

|                        |                                                                               |
|------------------------|-------------------------------------------------------------------------------|
| Shell style / Model id | FG - Straight plug                                                            |
| Plug                   | Straight                                                                      |
| Housing material       | Brass (chrome plated [SAE AMS 2460]) shell and nut, other pieces brass        |
| Locking system         | Push-pull                                                                     |
| Keying                 | 3 keys (beta=165, gamma=30, plug: male contacts, receptacle: female contacts) |
| Weight                 | 17.36 g                                                                       |

[https://www.lemo.com/int\\_en/solutions/optima/f-rugged-push-pull/fgn-2f-319-clc.html](https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/fgn-2f-319-clc.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


## Environment

|                                   |                                                                   |
|-----------------------------------|-------------------------------------------------------------------|
| Technical domain                  | Motorsport, Security and Defence                                  |
| Environmental sealing (IP rating) | IP67                                                              |
| Endurance                         | 5000 mating cycles                                                |
| Temperature range                 | -55°C / +200°C (max. temperature valid for short periods of use.) |
| Climatical Category               | 50/175/21 (Aluminium shell)                                       |
| Humidity (max)                    | <=95% [at 60 deg C /140 F]                                        |
| Shock Resistance                  | 100 g [ 6 ms]                                                     |
| Vibration                         | 15 g [10 Hz - 2000 Hz]                                            |
| Salt Spray Corrosion              | >1000 hr                                                          |

## Cable fixation

|                                    |                 |
|------------------------------------|-----------------|
| Cable termination protection       | Heatshrink      |
| Fixation type                      | Heatshrink      |
| Jacket cable outside diameter [mm] | 5.30 - 14.00 mm |

## Drawings



## Dimensions

|     | M    | A    | B    | L    | X    |
|-----|------|------|------|------|------|
| mm. | 17.9 | 17   | 14   | 27.8 | 8    |
| in. | 0.7  | 0.67 | 0.55 | 1.09 | 0.31 |

[https://www.lemo.com/int\\_en/solutions/optima/f-rugged-push-pull/fgn-2f-319-clc.html](https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/fgn-2f-319-clc.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Recommended By Lemo

| Accessories         |                                |
|---------------------|--------------------------------|
| Replacement contact | <a href="#">FGG.0B.555.ZZC</a> |
| Compatible cap      | <a href="#">BFG.2F.100.XAZ</a> |
| Tools               |                                |
| Positionner         | <a href="#">DCE.91.070.BVC</a> |
| Extraction tool     | <a href="#">DCF.93.070.4LT</a> |
| Crimp tool          | <a href="#">DPC.91.701.V</a>   |

## Cables

| Cable PartNumber   | Material      | Colour | Cable image                                                                         |
|--------------------|---------------|--------|-------------------------------------------------------------------------------------|
| CMN.19.T22.079QGZE | TPR (medical) | Grey   |  |