



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[Catalog](#)

[Customer Drawing](#)

Jacket cable outside diameter [mm]	3.80 - 9.00 mm
Size	0F
Series	F - Rugged Push-Pull

[https://www.lemo.com/int\\_en/solutions/optima/f-rugged-push-pull/gec-0f-240-rr.html](https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/gec-0f-240-rr.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

Form & Material	
Shell style / Model id	GEC - Conical nuts
Keying	No keying
Weight	0.3 g
Environment	
Technical domain	Motorsport, Security and Defence
Environmental sealing (IP rating)	No IP rating
Temperature range in water steam	+140°C
Cable fixation	
Jacket cable outside diameter [mm]	3.80 - 9.00 mm