



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[Catalog](#)

[Customer Drawing](#)

|                                    |                                                                   |
|------------------------------------|-------------------------------------------------------------------|
| Number of contacts Low Voltage     | 5                                                                 |
| Wire Size/AWG                      | 30 - 22                                                           |
| Gender                             | Standard                                                          |
| Plug                               | Plug - Straight                                                   |
| Locking system                     | Push-pull                                                         |
| Jacket cable outside diameter [mm] | 5.30 - 6.50 mm                                                    |
| Size                               | 1P                                                                |
| Suggested matching part            | <a href="#">PLG.M0.5GL.LG</a><br><a href="#">PRG.M0.5GL.LC65G</a> |
| Series                             | REDEL P - Push-Pull                                               |

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/pag-m0-5gl-ac65g.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pag-m0-5gl-ac65g.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

|                                 |                               |
|---------------------------------|-------------------------------|
| Number of contacts Low Voltage  | 5                             |
| Contact Termination Low voltage | Solder                        |
| R (max)                         | 4.5 mOhm                      |
| Insert configuration value      | 1P.M05 - 5 Low Voltage        |
| Insulator                       | L: PEEK (UL 94 / V-0/1.5)     |
| Rated current                   | 7 A                           |
| Test voltage contact-contact    | 1.48 (kV DC)                  |
| Max. Solid Conductor            | 0.34 mm <sup>2</sup> (AWG 22) |
| Max. Stranded Conductor         | 0.34 mm <sup>2</sup> (AWG 22) |
| Air clearance                   | 0.8 mm                        |
| Creepage distance               | 0.8 mm                        |
| Bucket Dia.                     | 0.8 mm (0.031in)              |
| Contact Dia.                    | 0.9 mm (0.035in)              |
| Wire Size/AWG                   | 30 - 22                       |
| Gender                          | Standard                      |

## Form & Material

|                        |                                                                      |
|------------------------|----------------------------------------------------------------------|
| Shell style / Model id | PA - Straight plug with cable collet                                 |
| Plug                   | Straight                                                             |
| Housing material       | PSU (Polysulfone), grey                                              |
| Locking system         | Push-pull                                                            |
| Keying                 | G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts) |
| Colour                 | Grey                                                                 |
| Variant                | Grey collet nut                                                      |
| Weight                 | 4.94 g                                                               |

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/pag-m0-5gl-ac65g.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pag-m0-5gl-ac65g.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Environment

|                                   |                                                                                                                                                                                                     |
|-----------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Technical domain                  | Energy and Industrial, Medical, Test and Measurement, Transportation, Aerospace and UAV                                                                                                             |
| Environmental sealing (IP rating) | IP50                                                                                                                                                                                                |
| Endurance                         | > 5000 mating cycles                                                                                                                                                                                |
| Temperature range                 | -50°C / +150°C                                                                                                                                                                                      |
| F ret (max)                       | 150 N                                                                                                                                                                                               |
| F ret (min)                       | 50 N                                                                                                                                                                                                |
| Steam sterilization               | Fully sterilizable (Steam, Gamma, ETO) following our protocols and tests in line with ISO 11134 and IEC 60601-1 standards. For more details on sterilization methods and cycles, please contact us. |

## Cable fixation

|                                    |                                              |
|------------------------------------|----------------------------------------------|
| Cable termination protection       | Standard back nut (no additional protection) |
| Fixation type                      | Cable collet                                 |
| Jacket cable outside diameter [mm] | 5.30 - 6.50 mm                               |

# CAD

## Documents

Eplan [Download](#)

# Cables

| Cable PartNumber | Material | Colour | Cable image                                                                           |
|------------------|----------|--------|---------------------------------------------------------------------------------------|
| 150250           | PVC      | Grey   |  |

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/pag-m0-5gl-ac65g.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pag-m0-5gl-ac65g.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.