



Image for illustrative purpose only

Summary

[Request a quote](#)

[Catalog](#)

Number of contacts High Voltage	1
Wire Size/AWG	30 - 22
Socket / Receptacle	Socket / Receptacle - Fixed Panel Rear Mounted
Locking system	Push-pull
Size	5
Suggested matching part	FFR.05.403.LLAE141

https://www.lemo.com/int_en/pes-05-403-llle141.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Number of contacts High Voltage	1
Contact Termination High voltage	Solder
Rated current	4 A
Contact resistance	<8 mOhms
Test voltage	12kV (dc) / 1 min
Contact Dia.	0.7
Wire Size/AWG	30 - 22

Form & Material

Shell style / Model id	PES - Fixed receptacle, nut fixing, with cable crimping (back panel mounting)
Socket / Receptacle	Fixed Panel Rear Mounted
Housing material	Aluminum alloy (anodized) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, female
Weight	2.05 g

Environment

Environmental sealing (IP rating)	IP50
Endurance	>200 mating cycles
Radiation resistance	10e6 Gray
Working temperature	-20 deg C to + 125 deg C


Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Crimp

Drawings

https://www.lemo.com/int_en/pes-05-403-IIIe141.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



Dimensions

	L	A
mm.	42	8.5
in.	1.65	0.33