


Jul.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



Note 1. Per pack : 100 pieces.
2. UL (File No.E52653)
C-UL (File No.E52653)
TÜV (Certificate No.R50244085) authorization article.




				1		PBT		BLACK, UL94V-0											
NO.		MATERIAL		FINISH . REMARKS				NO.		MATERIAL		FINISH . REMARKS							
UNITS mm				SCALE 2 : 1				COUNT		DESCRIPTION OF REVISIONS				DESIGNED		CHECKED		DATE	
HIROSE ELECTRIC CO., LTD.				APPROVED : KI. AKIYAMA				14. 06. 06		DRAWING NO.		EDC3-344823-01							
				CHECKED : TS. FUKUSHIMA				14. 06. 06		PART NO.		DF60-4EP-10. 16C							
				DESIGNED : TS. KUMAZAWA				14. 06. 06		CODE NO.		CL680-3027-0-00							
				DRAWN : TS. KUMAZAWA				14. 06. 06				1/2							


Jul.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

DF60 In-Line type recommended panel mounting manual (When nuts uses)


Nut installation process



1. Slide a nut (Size:M3) to nut fix part.




2. Press down the nut until it clicks, then this sound means the nut has inserted into nut holder.




Panel mounting process

1. Insert connector into panel cut out part.



2. Tighten a screw (Size:M3) to fix with panel.
recommended torque : less than 49N · cm



HRS

DRAWING NO.	EDC3-344823-01
PART NO.	DF60-4EP-10.16C
CODE NO.	CL680-3027-0-00

2/2