


Oct.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



NOTES) 1. PARTS ①⑧⑨ ARE DELIVERED ASSEMBLED.
PARTS ②③④⑤⑥⑦ ARE DELIVERED DISASSEMBLED.
2. OUTER DIAMETER OF APPLICABLE CABLE IS $\phi 6.2 \pm 0.3$.
3. DIMENSIONS IN PARENTHESES ARE SHOWN AS REFERENCES.

4	STEEL	SURFACE PLATING : NICKEL $3\mu\text{m}$ MIN. UNDER PLATING : COPPER $2\mu\text{m}$ MIN.	9	STAINLESS STEEL	
3	STEEL	SURFACE PLATING : NICKEL $3\mu\text{m}$ MIN. UNDER PLATING : COPPER $2\mu\text{m}$ MIN.	8	STEEL	SURFACE PLATING : NICKEL $2\mu\text{m}$ MIN. UNDER PLATING : COPPER $1\mu\text{m}$ MIN.
2	POLYCARBONATE	(GRAY), UL94V-0	7	BRASS	
1	POLYCARBONATE	(GRAY), UL94V-0	6	BRASS	
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED
HIROSE ELECTRIC CO., LTD.		APPROVED : YH. ENAMI	09.12.17	DRAWING NO.	EDC3-120648-01
		CHECKED : HO. MIWA	09.12.17	PART NO.	FI-20-CV7
		DESIGNED : HN. ANDO	09.12.17	CODE NO.	CL230-0525-2-00
		DRAWN : HN. ANDO	09.12.17		