





COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△				..	△				..
△				..	△				..
△				..	△				..



- NOTE 1 APPLICABLE WIRE: AWG#24~28(JACKET DIAMETER ϕ 1.15 MAX)
2 APPLICABLE CRIMPING TOOL: HR22-TA2428HC(CL150-0200-4)
3 APPLICABLE CRIMP CONTACT EXTRACTION TOOL: RP6-SC-TP(CL150-0039-0)
4 A PACKAGE CONTAINING 100 PIECES.

TO
R
USA

1	PHOSPHOR BRONZE SILVER PLATED								
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	CHECKED	APPROVED	RELEASED		
CODE NO. (OLD)									
DRAWING NO. EDC3-044336									
SCALE 10 : 1									
UNITS mm									
DRAWING NO. EDC3-044336									
PART NO. HR22-SC-122									
CODE NO. CL122-0016-6									
HRS HIROSE ELECTRIC CO., LTD									