






[illegible]

ISO VEW




SECTION A-A
SCALE 4:1



PIN NO.1

PIN NO 10



HRS MARKING

CAVITY NO.

NOTE

- NOTE
1. THE HARMFUL BURRS SHALL BE 0.1mm OR LESS.
 2. APPLICABLE TERMINAL

NO.	PART NAME	PART NO.
1	KM32A F TMI (I) (800)	6451-0044-2-800

UNLESS OTHERWISE SPECIFIED. SEE TABLE FOR TOLERANCES.			CODE NO. (OLD)		DRAWN		DESIGNED		CHECKED		APPROVED		RELEASED		
DIMENSION CLASSIFICATION OVER TO		公差 OTHER	DRAWING NAME												
	10	±0.15				CUSTOMER DRAWING			PART NAME. KM32A-10S-HU(B)(800)						
10	30	±0.2													
30	50	±0.3													
50	70	±0.4													
70	100	±0.5													
100	125	±0.75				EDC3-631677-00			PART NO. 6441-0060-2-800						
125	250	±0.9													
角度 ANGULAR ±0.5°			UNITS mm			 HIROSE KOREA CO.,LTD.			DRAWING SIZE A3			SHEET 1 /			