


NOTES 1. PER REEL:30000 CONTACTS.

2. APPLICABLE CABLE


CABLE SIZE : AWG28(7/0.127) TO AWG36(7/0.05)

OUTER DIAMETER : ϕ 0.27 TO 0.58mm

③ AVOID ANGLED INSERTION OF CRIMP CONTACT(MDF76-2836PCFA(41)) TO MAINTAIN PERFORMANCE RELIABILITY.



A-A (20 : 1)



B-B (20 : 1)






FIGURE OF INSERTION ③

HORIZONTALLY:OK



DIAGONAL:NG



NO.	MATERIAL	FINISH , REMARKS			NO.	MATERIAL	FINISH , REMARKS			
		UNITS mm	SCALE 10 : 1	COUNT			DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
							APPROVED : TS. SAKATA	10. 03. 24	DRAWING NO.	EDC3-310367-02
							CHECKED : TS. FUKUSHIMA	10. 03. 23	PART NO.	MDF76-2836PCFA(41)
							DESIGNED : TH. YOSHIZAWA	10. 03. 23	CODE NO.	CL547-0919-4-41
							DRAWN : YK. NAKATSU	10. 03. 23		
HIROSE ELECTRIC CO., LTD.	HRS									