


Apr.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



NOTES:1

APPLICABLE CABLE

	WIRE	INSULATOR OUTER DIAMETER 0.90 TO 1.00 DIA. CONDUCTOR SIZE (STRANDED) AWG26~27 OR EQUIVALET	
	VINYL SEATH OUTER DIAMETER	Ø5.0	*(1)
	DRAIN WIRE	AWG 25 OR EQUIVALENT 7/0.18 DIA.	*(2)

- *(1)CABLE ENTRY IS 5.6 MIN.
- *(2)CONSTRUCTION IS FOR REFERENCE.

ADAPTER

- 2 ADAPTER SHALL BE USED TO ALIGN INDIVIDUAL WIRE.
- 3 THE DIMENSION IN PARENTHESIS IS FOR REFERENCE.

2	PHOSPHOR BRONZE	UNDER :NICKEL PLATING 2µm min OVER :GOLD PLATING 1.27µm min	4	POLYCARBONATE	TRANSPARENCY
1	POLYCARBONATE	TRANSPARENCY	3	BRASS	UNDER :COPPER PLATING 0.5µm min OVER :TIN REFLOW PLATING 1µm min
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 4 : 1	COUNT 3	DESCRIPTION OF REVISIONS DIS-E-003517	
		APPROVED :HO. MIWA		DESIGNED	YH. MAMADA
		CHECKED :TH. KAMEYA		CHECKED	YH. ENAMI
		DESIGNED :SS. SATOH		DATE	10.11.26
		DRAWN :SS. SATOH		DRAWING NO. EDC3-120679-01	
				PART NO.	TM11AP-88P(01)
				CODE NO.	CL222-2780-6-01