



Cable Assemblies > Copper Cable Assemblies > Pluggable I/O Cable Assemblies



Cable Assembly (End A): **Socket Housing**

Cable Assembly (End B): **Socket Housing**

Wire Size: **.05 mm²**

Shielded: **No**

Features

Product Type Features

Cable Assembly (End A)	Socket Housing
Cable Assembly (End B)	Socket Housing
Cable Style	Ribbon Cable

Configuration Features

Number of Positions	16
---------------------	----

Electrical Characteristics

Impedance	125 Ω
-----------	-------

Body Features

Cable Color	Gray
Cable Flammability Rating	VW-1

Contact Features

Contact Mating Area Plating Material	Gold (Au)
--------------------------------------	-----------

Mechanical Attachment

Mating Alignment	With
------------------	------



Housing Features

Housing Material	LCP
------------------	-----

Dimensions

Wire Size	.05 mm²
-----------	---------

Operation/Application

Shielded	No
----------	----

Other

Cable Assembly Configuration	Double Ended
Cable Assembly Length	.2 m [.66 ft]

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 193893-E
IDCCS SMC 1,27 80 * AU AUI 300 PVC



TE Part # 193889-E
IDCCS SMC 1,27 68 * AU AUI 200 PVC



TE Part # 173801-E
IDCCS SMC 1,27 12 * AU AUI 300 PVC



TE Part # 173798-E
IDCCS SMC 1,27 26 * AU AUI 300 PVC



TE Part # 173795-E
IDCCS SMC 1,27 50 * AU AUI 300 PVC



TE Part # 254587-E
SMCQ 16 M AB VV 8-13 CL * H007 137 E005




TE Part # 168304-E
IDCCS SMC 1,27 16 * AU AUI 300 PVC




TE Part # 354094-E
SMCB 16 M AB VV 7-03 CL * 0007 137 E004

Also in the Series | ERNI SMC




Board-In Connectors(6)



Board-to-Board Headers & Receptacles(81)



Connector Adapters & Connector Savers(41)



PCB Headers & Receptacles(81)




Pluggable I/O Cable Assemblies(27)



Rectangular Power Connectors(86)




Wire-to-Board Connector Assemblies & Housings(5)



Wire-to-Board Headers & Receptacles (3)


Customers Also Bought



TE Part #254117-E
STVC 96 F ABC VV 7-00 EE 2,9 * 247 E007



TE Part #ANT-433-CW-HW
Antenna 1/4 Wave Whip 433MHz RPS



TE Part #594750-E
STVH15 15 F ZD VV 2 1206 4,3 * 197 E 172



TE Part #EXR420TN-001
Duck,EXR,420-450, MHz TNCM,







TE Part #234712-E
STVR 96 MI ABC VW 4-00 EE 6,0 * 247 E00



TE Part #20008669-50
MS5839-02BA36 CL RESISTANT LS T&R SEN




TE Part #292132-3
CT P/HDR BOX V 3P NAT



TE Part #2-534206-0
40 MODII VRT DR CE 100/115



TE Part #2-1445093-9
MICRO MNL HDR ASSY S/ROW AU LF



TE Part #2-2176397-0
3502 6R2 1%

Documents

CAD Files

Customer View Model

ENG_CVM_CVM_168303-E_1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_168303-E_1.3d_igs.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_168303-E_1.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Datasheet - ERNI SMC 1.27mm Connectors

English

Datasheet - ERNI SMC 1.27mm Connectors

Datasheet - ERNI SMC 1.27mm Connectors

German