



Application Tooling > Insertion & Extraction Tools



Insertion & Extraction Tool Type: **Contact Extraction**

Insertion & Extraction Tool Application: **Contact-to-Housing**

Features

Product Type Features

Insertion & Extraction Tool Type	Contact Extraction
Insertion & Extraction Tool Application	Contact-to-Housing

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-D9934-A83

Contact: Component To Wire ; 20-45A , 20-8 wire size

Also in the Series | Dynamic 5000 Series

Connector Contacts(43)

Connector Hardware(3)

Power Contacts(43)

Rectangular Connector Housings(61)

Rectangular Power Connectors(109)

Standard Rectangular Connectors(74)

Wire-to-Board Connector Assemblies & Housings(31)

Customers Also Bought

TE Part #EKB201N00330500000

915 EXTENSION

TE Part #91596-1

CCII D-5 SS REC TAB 20-16 ASSY

TE Part #CAT-D9934-A83

Contact: Component To Wire ; 20-45A , 20-8 wire size

TE Part #1366044-1

HHHT DYNAMIC D-5 L 8 ASSY





TE Part #1376807-2

DYNATAP CONN. 18P ASSY -DYNAMI



TE Part #2-1827864-4

DYNAMIC 1200D REC HSG 8P Y
BLACK



TE Part #1-2069029-4

DYNAMIC 1500T REC HSG 12P X
BLACK



TE Part #2119142-1

CCII D1000 2L REC TAB 22-18 ASSY



TE Part #EKB001N00320001000

615 EXTENSION

Documents

Instruction Sheets

Instruction Sheet (non U.S.)

English

Extraction Tool for AMP Dynamic D-5000 Series

English