

SS M3 D 128-A 3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

Version	Lock washer, Copper
Order No.	0164400000
Type	SS M3 D 128-A 3
GTIN (EAN)	4008190035914
Qty.	50 pc(s).

SS M3 D 128-A 3

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Diameter	6.2 mm	Wall thickness, max.	1.2 mm
Net weight	0.1 g		

Temperatures

Ambient temperature	-5 °C...40 °C
---------------------	---------------

Material data

Material	Copper	Surface finish	untreated
Colour	grey		

System specifications

Version	Fuse cartridge
---------	----------------

Additional technical data

Installation advice	Direct mounting	Type of mounting	Rail
---------------------	-----------------	------------------	------

Dimensions

Diameter	6.2 mm
----------	--------

General

Installation advice	Direct mounting	Surface finish	untreated
---------------------	-----------------	----------------	-----------

Classifications

ETIM 6.0	EC002345	ETIM 7.0	EC002345
ETIM 8.0	EC002345	ETIM 9.0	EC002345
ETIM 10.0	EC002345	ECLASS 9.0	23-09-03-06
ECLASS 9.1	23-09-92-90	ECLASS 10.0	23-09-92-90
ECLASS 11.0	23-09-03-06	ECLASS 12.0	23-09-03-09
ECLASS 13.0	23-09-03-09	ECLASS 14.0	23-09-03-09
ECLASS 15.0	23-09-03-09		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
Brochures	