

BFSC M4X20**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Depending on the terminal block or also accessories, we offer different types of screws as additional items or also spare parts.

General ordering data

Version	Mounting screw (Terminal), 4.00 mm, Steel, Depth: 7 mm, Width: 7 mm, Height: 20 mm
Order No.	0362800000
Type	BFSC M4X20
GTIN (EAN)	4008190114053
Qty.	100 pc(s).

BFSC M4X20**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	7 mm	Depth (inches)	0.276 inch
Height	20 mm	Height (inches)	0.787 inch
Width	7 mm	Width (inches)	0.276 inch
Diameter	4 mm	Net weight	2.11 g

Temperatures

Ambient temperature	-5 °C...40 °C
---------------------	---------------

Material data

Material	Steel	Colour	silver
----------	-------	--------	--------

System specifications

Version	for cross-connection link
---------	---------------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in	Type of mounting	when screwed in

Dimensions

Diameter	4 mm	Metric size of the thread, external	4 mm
----------	------	-------------------------------------	------

General

Installation advice	Direct mounting
---------------------	-----------------

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 9.0	27-14-11-92
ECLASS 9.1	27-14-11-92	ECLASS 10.0	27-14-11-92
ECLASS 11.0	27-14-11-92	ECLASS 12.0	27-14-11-92
ECLASS 13.0	27-25-03-90	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------