

IE-OP-V04P-1S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Junction box, design for PushPull plug-in connectors ver.4
according to IEC 61076-3-106, plastic

General ordering data

Version	Wall-mounted junction box, IP67, Variant 4 to IEC 61076-3-106
Order No.	1045780000
Type	IE-OP-V04P-1S
GTIN (EAN)	4032248779963
Qty.	10 pc(s).

IE-OP-V04P-1S

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	106.9 mm	Depth (inches)	4.209 inch
Height	61.6 mm	Height (inches)	2.425 inch
Width	41.8 mm	Width (inches)	1.646 inch
Net weight	6.5 g		

Temperatures

Operating temperature	-40 °C...70 °C
-----------------------	----------------

General data

Colour	black	Housing main material	PA
Plugging cycles	750	Protection degree	IP67
Type of mounting	Floor-mounted, for exposed connections, Wall mounting	UL 94 flammability rating	V-0

General standards

Connector standard	IEC 61076-3-106 Var. 4
--------------------	------------------------

Classifications

ETIM 7.0	EC002597	ETIM 8.0	EC002597
ETIM 9.0	EC002597	ETIM 10.0	EC002597
ECLASS 9.1	27-44-03-18	ECLASS 10.0	27-44-03-18
ECLASS 11.0	27-44-03-18	ECLASS 12.0	27-44-03-18
ECLASS 13.0	27-44-03-18	ECLASS 14.0	27-44-03-18
ECLASS 15.0	27-44-03-18		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	MB FREECONTACT EN FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN

IE-OP-V04P-1S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing

