

IE-KSF-PKV14M-KLROB-10M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Assembled IE cables

General ordering data

Version	
Order No.	1103660100
Type	IE-KSF-PKV14M-KLROB-10M
GTIN (EAN)	4032248918409
Qty.	1 pc(s).

IE-KSF-PKV14M-KLROB-10M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	1,287 g
------------	---------

Temperatures

Operating temperature	-40 °C...70 °C
-----------------------	----------------

Electrical properties

Operating voltage	30 V
-------------------	------

General standards

Connector standard	IEC 61076-3-119 CDV, IEC 61076-3-117 Var. 14
--------------------	--

Standards

Connector standard	IEC 61076-3-119 CDV, IEC 61076-3-117 Var. 14
--------------------	--

Cable structure

Sheath diameter, max.	9.3 mm	Sheathing colour	black (similar to RAL 9005)
-----------------------	--------	------------------	-----------------------------

Electrical properties of cable

Operating voltage	30 V
-------------------	------

Mechanical and material properties of cable

Min. bending radius, once only	5 x cable diameter	Min. bending radius, repetitive	10 x cable diameter
--------------------------------	--------------------	---------------------------------	---------------------

Classifications

ETIM 6.0	EC001579	ETIM 7.0	EC001579
ETIM 8.0	EC001579	ETIM 9.0	EC001579
ETIM 10.0	EC001579	ECLASS 9.0	27-06-24-90
ECLASS 9.1	27-06-24-00	ECLASS 10.0	27-06-05-01
ECLASS 11.0	27-06-05-01	ECLASS 12.0	27-06-05-01
ECLASS 13.0	27-06-05-01	ECLASS 14.0	27-06-05-01
ECLASS 15.0	27-06-05-01		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1

Approvals

ROHS	Conform
------	---------

IE-KSF-PKV14M-KLROB-10M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

User Documentation

[MAN IE GUIDE DE](#)

[MAN IE GUIDE EN](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

[FL FIELDWIRING EN](#)

[PI PROFINET CABLING EN](#)

IE-KSF-PKV14M-KLROB-10M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings