

IE-PIC-HYB-S-0,2-300

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Hybrid, 10-pole. Inserts for plug-in connectors Variant 14

General ordering data

Version	Crimp contact, for plug insert, Hybrid
Order No.	1135150000
Type	IE-PIC-HYB-S-0,2-300
GTIN (EAN)	40322489 15347
Qty.	300 pc(s).

IE-PIC-HYB-S-0,2-300

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	0.27 g
------------	--------

General data

Wire connection cross section, finely stranded, max.	0.2 mm ²	Wire connection cross section, finely stranded, min.	0.08 mm ²
--	---------------------	--	----------------------

Electrical properties

Rated voltage	24 V
---------------	------

Classifications

ETIM 6.0	EC001121	ETIM 7.0	EC001121
ETIM 8.0	EC001121	ETIM 9.0	EC001121
ETIM 10.0	EC001121	ECLASS 9.0	27-44-03-90
ECLASS 9.1	27-44-09-90	ECLASS 10.0	27-44-03-90
ECLASS 11.0	27-44-03-90	ECLASS 12.0	27-44-03-90
ECLASS 13.0	27-44-03-90	ECLASS 14.0	27-44-03-90
ECLASS 15.0	27-44-03-90		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Important note

Product information	Hybrid, 10-pole. Inserts for plug-in connectors Variant 14
---------------------	--

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	PROFINET Manufacturer's Declaration
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN Designation key / Type key
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN

IE-PIC-HYB-S-0,2-300

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing

