

VKSW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Wire channel cutter for manual operation in cutting wiring channels and covers up to 125 mm wide and a wall thickness of 2.5 mm. Only for plastics not reinforced by fillers.

- Cutting with no burrs or waste
- Length stop (1,000 mm) with guide device for precise cutting to length
- Table-top unit for mounting on a workbench or similar work surface
- Hardened cutting edges made of special steel

General ordering data

Version	Cable duct cutting device
Order No.	1137530000
Type	VKSW
GTIN (EAN)	4032248919406
Qty.	1 pc(s).

VKSW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	290 mm	Depth (inches)	11.417 inch
Height	285 mm	Height (inches)	11.22 inch
Width	280 mm	Width (inches)	11.024 inch
Net weight	305 g		

Cutting tools

Cutting width max.	125 mm
--------------------	--------

Classifications

ETIM 6.0	EC000149	ETIM 7.0	EC000149
ETIM 8.0	EC000149	ETIM 9.0	EC000149
ETIM 10.0	EC000149	ECLASS 9.0	21-04-50-03
ECLASS 9.1	21-01-90-90	ECLASS 10.0	21-04-50-03
ECLASS 11.0	21-04-50-03	ECLASS 12.0	21-04-50-03
ECLASS 13.0	21-04-50-03	ECLASS 14.0	21-04-50-03
ECLASS 15.0	21-04-50-03		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Downloads

Catalogues	Catalogues in PDF-format
Brochures	