

INLAY CC-M 58/35**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Order No.	1415950000
Type	INLAY CC-M 58/35
GTIN (EAN)	4050118217254
Qty.	1 pc(s).

INLAY CC-M 58/35**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	120 mm	Depth (inches)	4.724 inch
Height	8 mm	Height (inches)	0.315 inch
Width	76 mm	Width (inches)	2.992 inch
Net weight	74 g		

General data

Operating temperature range, max.	130 °C	Operating temperature range, min.	-55 °C
Version	Holder for 10 signs	Width	76 mm

Classifications

ETIM 6.0	EC001675	ETIM 7.0	EC001675
ETIM 8.0	EC001675	ETIM 9.0	EC001675
ETIM 10.0	EC001675	ECLASS 9.0	19-14-92-90
ECLASS 9.1	19-14-92-90	ECLASS 10.0	19-14-92-90
ECLASS 11.0	19-14-90-90	ECLASS 12.0	19-14-90-90
ECLASS 13.0	19-14-90-90	ECLASS 14.0	19-14-90-90
ECLASS 15.0	19-14-90-90		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

INLAY CC-M 58/35

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Example of use

