

AKKU DMS PRO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Only for Europe



Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

General ordering data

Version	Mounting tool
Order No.	1479110000
Type	AKKU DMS PRO
GTIN (EAN)	4050118348712
Qty.	1 pc(s).

AKKU DMS PRO

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	70 g
------------	------

Technical data

Charging time	30 min	Description of article	Battery for DMS PRO
---------------	--------	------------------------	---------------------

Electric screwdriver

Battery voltage	3.6 V	Bit holder	1/4" DIN 3126 Form E6.3
Charger input	AC 220-240V~50-60Hz 30W	Charger output	DC 2.8...6V; 4.8A / 30W max.
Charging time	30 min	Idling speed	200 u. 600 min ⁻¹
Max. coupling torque	3 Nm	Rated voltage	3.6 V
Rechargeable batteries	Li-Ion battery		

Classifications

ETIM 6.0	EC001199	ETIM 7.0	EC001199
ETIM 8.0	EC001199	ETIM 9.0	EC001199
ETIM 10.0	EC001199	ECLASS 9.0	21-05-92-07
ECLASS 9.1	21-05-92-07	ECLASS 10.0	21-05-92-07
ECLASS 11.0	21-05-29-02	ECLASS 12.0	21-05-29-02
ECLASS 13.0	21-05-29-02	ECLASS 14.0	21-05-29-02
ECLASS 15.0	21-05-29-02		

Approvals

ROHS	Conform
------	---------

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

Downloads

Catalogues	Catalogues in PDF-format
Brochures	