

KSI/0,1-0,5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Insulated pin-cable connector made from PVC or PC/PA**

- Conventional designs
- Not soldered
- With conical entry funnel

General ordering data

Version	cable lug, terminal end, Insulated cable connector, 0.5 mm ² , 0.1 mm ² - 0.5 mm ²
Order No.	1491370000
Type	KSI/0,1-0,5
GTIN (EAN)	4050118301625
Qty.	100 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2026-03-31

KSI/0,1-0,5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	0.268 g
------------	---------

Connectors

Conductor cross-section	0.5 mm ²	Conductor cross-section, max.	0.5 mm ²
Conductor cross-section, min.	0.1 mm ²	Identification colour	yellow
Inside diameter of collar (d4)	2.2 mm	Inside diameter of shaft (d1)	1 mm
Insulation	Available, PA	Length 1 (l1)	18 mm
Length 2 (l2)	9 mm	Material/plastic	PA
Outside diameter of shaft (d3)	1.2 mm		

Classifications

ETIM 6.0	EC001059	ETIM 7.0	EC001059
ETIM 8.0	EC001059	ETIM 9.0	EC001059
ETIM 10.0	EC001059	ECLASS 9.0	27-40-02-92
ECLASS 9.1	27-40-02-12	ECLASS 10.0	27-40-02-92
ECLASS 11.0	27-40-02-92	ECLASS 12.0	27-40-02-92
ECLASS 13.0	27-40-02-92	ECLASS 14.0	27-40-02-92
ECLASS 15.0	27-40-02-92		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
Brochures	

KSI/0,1-0,5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

