

HSS-HF 4.8-9.5 EL W30M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

Version	Conductor and cable markers, 4.8 - 9.5 mm, white
Order No.	1513290000
Type	HSS-HF 4.8-9.5 EL W30M
GTIN (EAN)	4050118320848
Qty.	1 pc(s).
compatible printer	2599430000 2599440000

HSS-HF 4.8-9.5 EL W30M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	1.2 mm	Depth (inches)	0.047 inch
Width	15.1 mm	Width (inches)	0.594 inch
Length	30,000 mm	Length (inches)	1,181.1 inch
Net weight	562 g		

Temperatures

Operating temperature range	-55...105 °C
-----------------------------	--------------

General data

Colour	white	Halogen	No
Length	30,000 mm	Material	Polyolefine
Number per roll	1	Operating temperature range	-55...105 °C
Operating temperature range, max.	105 °C	Operating temperature range, min.	-55 °C
Printed characters	without	Type of printing	neutral
Width	15.1 mm		

Conductor and cable markers

Conductor O.D.	4.8 - 9.5 mm	Conductor O.D., max.	9.5 mm
Conductor O.D., min.	4.8 mm	Conductor cross-section, max.	16 mm ²
Conductor cross-section, min.	4 mm ²	Cross-section for connected wire	4 - 16 mm ²
Halogen	No	Rate of shrinkage	2:1
Recommended shrinking temperature	90 °C		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02
ECLASS 13.0	27-28-11-02	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Important note

Product information	External roll holder 1302920000 necessary
---------------------	---

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	NFX 70-100-1 2006 + NF X 70-100-2 2006 BS EN ISO 4589-2 1999 EN 45545-2:2020
Catalogues	Catalogues in PDF-format

Creation date June 16, 2025 9:55:50 PM CEST

HSS-HF 4.8-9.5 EL W30M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

