

IE-FC-SET-IPDEK001-KY-P**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, FrontCom® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the FrontCom® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

General ordering data

Version	FrontCom, Set
Order No.	1543680000
Type	IE-FC-SET-IPDEK001-KY-P
GTIN (EAN)	4050118348842
Qty.	1 pc(s).
Reference product	1450520000 1450630000 1450730000 1019570000 1962840000 1450820000

IE-FC-SET-IPDEK001-KY-P

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	134 mm	Depth (inches)	5.276 inch
Height	40 mm	Height (inches)	1.575 inch
Width	67 mm	Width (inches)	2.638 inch
Net weight	493.15 g		

General data

Material cover	Polycarbonate PC		
Material frame	Zinc diecast		
Product type	Set		
Protection degree	IP65, in closed state		
Reference product	Cardinality	1	
	Reference	IE-FC-SFP-KEY2	
	Cardinality	1	
	Reference	IE-FC-IP-PWB/2ST	
	Cardinality	1	
	Reference	IE-FC-IP-PWB-DE	
	Cardinality	1	
	Reference	IE-BI-USB-A	
	Cardinality	1	
	Reference	IE-BI-RJ45-C	
	Cardinality	1	
	Reference	IE-FC-PWPC	

Technical data

Data inserts	USB 2.0 A/A, RJ45 coupling Cat.6 _A	Frame	Plastic cover, Lockable with key
Insert plate	2x data, 1x power, Unshielded	Power inserts	Socket DE
Printing	Incl. fixed inscription: "Service only!", "USB", "Ethernet", "230 V AC"	Rated current for socket	16 A
Rated voltage for socket	250 V		

General standards

Certificate No. (DNV)	TAA000022B
-----------------------	------------

Classifications

ETIM 6.0	EC001031	ETIM 7.0	EC001031
ETIM 8.0	EC001031	ETIM 9.0	EC001031
ETIM 10.0	EC001031	ECLASS 9.0	27-18-27-02
ECLASS 9.1	27-18-27-90	ECLASS 10.0	27-18-27-02
ECLASS 11.0	27-18-27-02	ECLASS 12.0	27-18-28-92
ECLASS 13.0	27-18-28-92	ECLASS 14.0	27-18-28-92
ECLASS 15.0	27-18-28-92		

IE-FC-SET-IPDEK001-KY-P**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Approvals**

Approvals



Approvals MAMID	https://mdcop.weidmueller.com/mediadelivery/rendition/900_319234/-T1z1mm-S800/
ROHS	Conform

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	8a473a8a-33d4-4318-8088-c28f019e7f77

Downloads

Approval/Certificate/Document of Conformity	GL_FrontCom
Engineering Data	CAD data – STEP CAD data – DWG CAD data – DXF
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN

IE-FC-SET-IPDEK001-KY-P

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

