

**HSS-HF 12.7-25.4EL G30M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

**General ordering data**

|                    |                                                       |
|--------------------|-------------------------------------------------------|
| Version            | Conductor and cable markers, 12.7 - 25.4 mm, green    |
| Order No.          | <a href="#">1563040000</a>                            |
| Type               | HSS-HF 12.7-25.4EL G30M                               |
| GTIN (EAN)         | 4050118367591                                         |
| Qty.               | 1 pc(s).                                              |
| compatible printer | <a href="#">2599430000</a> <a href="#">2599440000</a> |

**HSS-HF 12.7-25.4EL G30M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |           |                 |              |
|------------|-----------|-----------------|--------------|
| Depth      | 1.5 mm    | Depth (inches)  | 0.059 inch   |
| Width      | 40.5 mm   | Width (inches)  | 1.594 inch   |
| Length     | 30,000 mm | Length (inches) | 1,181.1 inch |
| Net weight | 1,567 g   |                 |              |

**Temperatures**

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -55...105 °C |
|-----------------------------|--------------|

**General data**

|                                   |           |                                   |              |
|-----------------------------------|-----------|-----------------------------------|--------------|
| Colour                            | green     | Halogen                           | No           |
| Length                            | 30,000 mm | Material                          | Polyolefine  |
| Number per roll                   | 1         | Operating temperature range       | -55...105 °C |
| Operating temperature range, max. | 105 °C    | Operating temperature range, min. | -55 °C       |
| Printed characters                | without   | Type of printing                  | neutral      |
| Width                             | 40.5 mm   |                                   |              |

**Conductor and cable markers**

|                                   |                    |                                  |                          |
|-----------------------------------|--------------------|----------------------------------|--------------------------|
| Conductor O.D.                    | 12.7 - 25.4 mm     | Conductor O.D., max.             | 25.4 mm                  |
| Conductor O.D., min.              | 12.7 mm            | Conductor cross-section, max.    | 120 mm <sup>2</sup>      |
| Conductor cross-section, min.     | 35 mm <sup>2</sup> | Cross-section for connected wire | 35 - 120 mm <sup>2</sup> |
| Halogen                           | No                 | Rate of shrinkage                | 2:1                      |
| Recommended shrinking temperature | 90 °C              |                                  |                          |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 9.0  | 27-40-04-01 |
| ECLASS 9.1  | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |
| ECLASS 13.0 | 27-28-11-02 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**Important note**

|                     |                                           |
|---------------------|-------------------------------------------|
| Product information | External roll holder 1302920000 necessary |
|---------------------|-------------------------------------------|

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                                             |                                                                                                                                    |
|---------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">NEX 70-100-1 2006 + NF X 70-100-2 2006</a><br><a href="#">BS EN ISO 4589-2 1999</a><br><a href="#">EN 45545-2:2020</a> |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>                                                                                           |

Creation date May 7, 2025 12:39:40 PM CEST

**HSS-HF 12.7-25.4EL G30M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

Drawings

