

RD 16/11**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	Gauge rings, Adapter, PG 16 ,PG 11, IP54, Brass, nickel-plated
Order No.	1656110000
Type	RD 16/11
GTIN (EAN)	4008190409128
Qty.	50 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2024-05-17

RD 16/11

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	9.8 g
------------	-------

Temperatures

Operating temperature	-40 °C... 100 °C
-----------------------	------------------

General information

External thread	PG 16	Internal thread	PG 11
Material	Brass, nickel-plated	Note: protection class	Please follow the operating instructions to attain higher IP protection.
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Protection degree	IP54	Protection degree with GWDR	IP54

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 9.0	27-14-44-14
ECLASS 9.1	27-14-44-90	ECLASS 10.0	27-14-44-14
ECLASS 11.0	27-14-44-14	ECLASS 12.0	27-14-44-14
ECLASS 13.0	27-14-44-14	ECLASS 14.0	27-14-44-14
ECLASS 15.0	27-14-44-14		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	69c399a3-d29f-4fa4-b22e-340c0db02257

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--