

LM WO 36/93 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



Self-adhesive polyester labels which are suitable for A4 office laser printer.

General ordering data

Version	LaserMark, Conductor and cable markers, 9.5 - 22.3 mm, 36 x 93 mm, white
Order No.	1695741044
Type	LM WO 36/93 WS
GTIN (EAN)	4008190924720
Qty.	10 pc(s).

LM WO 36/93 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.025 mm	Depth (inches)	0.001 inch
Height	36 mm	Height (inches)	1.417 inch
Width	93 mm	Width (inches)	3.661 inch
Net weight	10 g		

Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

General data

Adhesive	Acrylate	
Colour	white	
Halogen	No	
Material	Polyester film	
Material colour according to resistance code	9	
Number of markers per combination	1 Label sheet = 15 Conductor and cable markers	
Number of markers per packaging unit	150	
Number of markers per packaging unit	Number of markers per combination	15
	Number of combinations per packaging unit	10
	Form of supply	Label sheet
Number per sheet	15	
Operating temperature range	-40...150 °C	
Operating temperature range, max.	150 °C	
Operating temperature range, min.	-40 °C	
Printed characters	without	
Size of labelling field	36 x 25 mm	
Type of printing	neutral	
UL 94 flammability rating	V-0	
Version	Self-adhesive	
Width	93 mm	

Conductor and cable markers

Conductor O.D.	9.5 - 22.3 mm	Conductor O.D., max.	22.3 mm
Conductor O.D., min.	9.5 mm	Conductor cross-section, max.	120 mm ²
Conductor cross-section, min.	25 mm ²	Cross-section for connected wire	25 - 120 mm ²
Halogen	No	Text field height	25 mm
Text field width	35.5 mm		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02
ECLASS 13.0	27-28-11-02	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

LM WO 36/93 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

