

**CBH 19/19 BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Fastening of cables or bundles with ties into electrical switchgears and cabinets.

**General ordering data**

|            |                                       |
|------------|---------------------------------------|
| Version    | Cable ties, 19 x 19 mm, Plastic, 80 N |
| Order No.  | <a href="#">1697950000</a>            |
| Type       | CBH 19/19 BK                          |
| GTIN (EAN) | 4008190883027                         |
| Qty.       | 100 pc(s).                            |

## CBH 19/19 BK

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Depth      | 2 mm   | Depth (inches)  | 0.079 inch |
| Height     | 19 mm  | Height (inches) | 0.748 inch |
| Width      | 19 mm  | Width (inches)  | 0.748 inch |
| Length     | 2 mm   | Length (inches) | 0.079 inch |
| Net weight | 0.71 g |                 |            |

## Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -40...60 °C |
|-----------------------------|-------------|

## Installation materials

|                                   |        |                                   |               |
|-----------------------------------|--------|-----------------------------------|---------------|
| Diameter of fastening hole        | 4.1 mm | For re-opening                    | No            |
| Halogen                           | No     | Material                          | Plastic       |
| Max. cable tie width              | 3.6 mm | Operating temperature range, max. | 60 °C         |
| Operating temperature range, min. | -40 °C | Tensile strength                  | 80 N          |
| Tensile strength (Pound-force)    | 18 lbf | UL 94 flammability rating         | V-2           |
| UV-resistant                      | Yes    | Version                           | Self-adhesive |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000449    | ETIM 7.0    | EC000449    |
| ETIM 8.0    | EC000449    | ETIM 9.0    | EC000449    |
| ETIM 10.0   | EC000449    | ECLASS 9.0  | 23-15-90-07 |
| ECLASS 9.1  | 27-40-07-90 | ECLASS 10.0 | 27-40-07-90 |
| ECLASS 11.0 | 23-15-25-09 | ECLASS 12.0 | 23-15-25-09 |
| ECLASS 13.0 | 23-15-25-09 | ECLASS 14.0 | 23-15-25-22 |
| ECLASS 15.0 | 23-15-25-22 |             |             |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|                  |                                          |
|------------------|------------------------------------------|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |

## CBH 19/19 BK

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Dimensioned drawing

