

SCT 4.6/127 C**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Weidmüller stainless steel Series contains a comprehensive assortment of stainless steel cable ties for extreme conditions such as high temperatures or severe chemical effects.

- stainless steel AISI 316,
- ideal for use outdoors,
- radiation- and corrosion-resistant,
- anti-magnetic,
- no serrations, so no damage to the insulation.

General ordering data

Version	Cable ties, 4.6 x 127 mm, Stainless steel 1.4301, 445 N
Order No.	1699800000
Type	SCT 4.6/127 C
GTIN (EAN)	4008190892241
Qty.	100 pc(s).
Available until	2022-10-31
Alternative product	2791380000

SCT 4.6/127 C

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.25 mm	Depth (inches)	0.01 inch
Height	127 mm	Height (inches)	5 inch
Width	4.6 mm	Width (inches)	0.181 inch
Net weight	1.6 g		

Temperatures

Operating temperature range	-80...538 °C
-----------------------------	--------------

Installation materials

Bundle diameter, max.	25 mm	Cable diameter, max.	25 mm
For re-opening	No	Halogen	No
Material	Stainless steel 1.4301	Operating temperature range, max.	538 °C
Operating temperature range, min.	-80 °C	Tensile strength	445 N
Tensile strength (Pound-force)	100 lbf	UL 94 flammability rating	None
UV-resistant	Yes		

Classifications

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ETIM 9.0	EC000046
ETIM 10.0	EC000046	ECLASS 9.0	27-14-07-02
ECLASS 9.1	27-14-07-02	ECLASS 10.0	27-14-07-02
ECLASS 11.0	27-14-07-02	ECLASS 12.0	27-14-07-02
ECLASS 13.0	27-14-07-02	ECLASS 14.0	27-14-07-02
ECLASS 15.0	27-14-07-02		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

Approvals



Approvals MAMID	https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/
ROHS	Conform

Downloads

Catalogues	Catalogues in PDF-format
------------	--

SCT 4.6/127 C

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing

