

KLBUE CO 2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****Shielding and earthing**

Our protective earth conductor and shielding terminals featuring different connection technologies allow you to effectively protect both people and equipment from interference, such as electrical or magnetic fields. A comprehensive range of accessories rounds off our range.

General ordering data

Version	Clamping yoke, Clamping yoke, Steel
Order No.	1752131001
Type	KLBUE CO 2
GTIN (EAN)	4032248064434
Qty.	10 pc(s).

KLBUE CO 2

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	41.6 mm	Depth (inches)	1.638 inch
Height	18 mm	Height (inches)	0.709 inch
Width	21.1 mm	Width (inches)	0.831 inch
Mounting dimension - width	20 mm	Net weight	18.7 g

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C

Material data

Material	Steel	Colour	silver
UL 94 flammability rating	None		

System specifications

Version	For a shield connection	End cover plate required	No
Rail	Busbar		

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting, Busbar
Type of fixing	Snap-on		

Conductors for clamping (rated connection)

Cable diameter, max.	15 mm	Cable diameter, min.	4 mm
Connection cross-section, stranded, max.	15 mm ²	Connection cross-section, stranded, min.	4 mm ²
Stripping length	18 mm	Type of connection	Spring connection

Dimensions

Pitch in mm (P)	18 mm
-----------------	-------

General

Installation advice	Direct mounting, Busbar	Rail	Busbar
---------------------	-------------------------	------	--------

Rating data

Rated cross-section	10 mm ²
---------------------	--------------------

Classifications

ETIM 6.0	EC002020	ETIM 7.0	EC002020
ETIM 8.0	EC002020	ETIM 9.0	EC002020
ETIM 10.0	EC002020	ECLASS 9.0	27-14-11-50
ECLASS 9.1	27-14-11-50	ECLASS 10.0	27-14-11-50
ECLASS 11.0	27-14-11-50	ECLASS 12.0	27-14-11-50
ECLASS 13.0	27-25-01-20	ECLASS 14.0	27-25-01-20
ECLASS 15.0	27-25-01-20		

KLBUE CO 2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	Beipackzettel_KLBUE.pdf StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	