

KLBUE 4-13.5 CPF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Thanks to special mounting feet, the product portfolio also includes shield clamping saddles that can be mounted on the C-profiles. The shield is diverted from the shield clamping saddles via the mounting foot to the C-profiles and thus to PE (ground).

General ordering data

Version	Clamping yoke, Clamping yoke, Steel
Order No.	1752691001
Type	KLBUE 4-13.5 CPF
GTIN (EAN)	4032248044429
Qty.	10 pc(s).

KLBUE 4-13.5 CPF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	31.5 mm	Depth (inches)	1.24 inch
Height	22 mm	Height (inches)	0.866 inch
Width	20.5 mm	Width (inches)	0.807 inch
Mounting dimension - width	19 mm	Net weight	23.1 g

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C

Material data

Material	Steel	Colour	grey
UL 94 flammability rating	None		

System specifications

Version	For a shield connection	End cover plate required	No
Rail	TS 27		

Additional technical data

Explosion-tested version	Yes	Installation advice	Direct mounting
Type of fixing	when screwed in		

Conductors for clamping (rated connection)

Cable diameter, max.	13.5 mm	Cable diameter, min.	4 mm
Connection cross-section, stranded, max.	13.5 mm ²	Connection cross-section, stranded, min.	4 mm ²
Stripping length	22 mm	Type of connection	Spring connection

Dimensions

Pitch in mm (P)	20 mm
-----------------	-------

General

Installation advice	Direct mounting	Rail	TS 27
---------------------	-----------------	------	-------

Rating data

Rated cross-section	10 mm ²
---------------------	--------------------

Classifications

ETIM 6.0	EC002020	ETIM 7.0	EC002020
ETIM 8.0	EC002020	ETIM 9.0	EC002020
ETIM 10.0	EC002020	ECLASS 9.0	27-14-11-50
ECLASS 9.1	27-14-11-50	ECLASS 10.0	27-14-11-50
ECLASS 11.0	27-14-11-50	ECLASS 12.0	27-14-11-50
ECLASS 13.0	27-25-01-20	ECLASS 14.0	27-25-01-20
ECLASS 15.0	27-25-01-20		

KLBUE 4-13.5 CPF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	Beipackzettel_KLBUE.pdf StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	