


HDC-CR24-7S GR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The sturdy CR24 module frames are available in polycarbonate or die-cast zinc.

The frames are designed so that 7 individual modules or corresponding double modules can be installed. The CR24 frames are designed to fit the size-8 housings.

General ordering data

Version	Heavy-duty connectors, HDC insert, ConCept frame
Order No.	1758500000
Type	HDC-CR24-7S GR
GTIN (EAN)	4032248019724
Qty.	5 pc(s).

HDC-CR24-7S GR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	111 mm	Depth (inches)	4.37 inch
Height	35 mm	Height (inches)	1.378 inch
Width	34 mm	Width (inches)	1.339 inch
Net weight	49.34 g		

Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

ConCept Pneumatic module

Colour	beige	UL 94 flammability rating	V-0
--------	-------	---------------------------	-----

Dimensions

Height of plug	35 mm	Total length base	111 mm
Width	34 mm		

General data

BG	8	Colour	beige
Free from halogens	false	Low smoke acc. DIN EN 45545-2	Yes
Material	Polycarbonate	Number of poles	1
Series	ConCept frame	Size	8
Type	Pin	UL 94 flammability rating	V-0

Connection data PE

Connection type PE	Screw connection	Tightening torque, max. PE connection	1.5 Nm
Tightening torque, min. PE connection	1.2 Nm		

Version

BG	8	Material	Polycarbonate
Size	8	Wire connection cross section AWG, max.	AWG 14

Classifications

ETIM 6.0	EC002312	ETIM 7.0	EC002312
ETIM 8.0	EC002312	ETIM 9.0	EC002312
ETIM 10.0	EC002312	ECLASS 9.0	27-44-02-06
ECLASS 9.1	27-44-02-06	ECLASS 10.0	27-44-02-06
ECLASS 11.0	27-44-02-06	ECLASS 12.0	27-44-02-92
ECLASS 13.0	27-44-02-92	ECLASS 14.0	27-44-02-92
ECLASS 15.0	27-44-02-92		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	2f94735a-9fba-4903-842f-4fb9aa902310

HDC-CR24-7S GR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS

Conform

Downloads

Engineering Data

[CAD data – STEP](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

[FL FIELDWIRING EN](#)