

SAI-SK STECKER M12**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Protective caps protect unassigned plug-in stations against external influences.

General ordering data

Version	Plug-in connector, IP20
Order No.	1781520000
Type	SAI-SK STECKER M12
GTIN (EAN)	4032248171835
Qty.	50 pc(s).

SAI-SK STECKER M12**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	0.82 g
------------	--------

Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...80 °C
---------------------	----------------	-----------------------	----------------

General technical data

Protection degree	IP20
-------------------	------

Classifications

ETIM 6.0	EC002314	ETIM 7.0	EC002314
ETIM 8.0	EC002314	ETIM 9.0	EC002314
ETIM 10.0	EC002314	ECLASS 9.0	27-44-02-92
ECLASS 9.1	27-44-02-08	ECLASS 10.0	27-44-02-92
ECLASS 11.0	27-44-02-08	ECLASS 12.0	27-44-02-08
ECLASS 13.0	27-44-02-08	ECLASS 14.0	27-44-02-08
ECLASS 15.0	27-44-02-08		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN