

HDC-CM-2SPN4.0**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Flexible and all-purpose – the proper solution for many applications**

ConCept is a modular system consisting of modules and frames. Together, they form a complete insert that can easily be integrated into an HDC housing.

The patented modular system allows you to put together individual connector variants.

A variety of modules for power, signal and data transmission are supplemented further by modules intended for pneumatics, and SC/LC cables.

The sturdy, one-piece module-frame design (optionally available in polycarbonate or die-cast zinc) and the integrated module-release aid both improve handling of the product.

General ordering data

Version	Heavy-duty connectors, HDC insert, ConCept module
Order No.	1894710000
Type	HDC-CM-2SPN4.0
GTIN (EAN)	4032248509188
Qty.	1 pc(s).

HDC-CM-2SPN4.0

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	25.4 mm	Height (inches)	1 inch
Width	11.4 mm	Width (inches)	0.449 inch
Length	34 mm	Length (inches)	1.339 inch
Net weight	15 g		

Temperatures

Limit temperature	-40 °C ... 80 °C
-------------------	------------------

ConCept Pneumatic module

Colour	black	Connection cross-section (internal)	4 mm
Contact travel	4 mm	Hose type	Only use PTFE hoses
Module body material	PA 6.6	Number of valves	2
Sealing material	NBR	Shutoff	No
Test pressure	10 bar	UL 94 flammability rating	V-0

Dimensions

Height of plug	25.4 mm	Total length base	34 mm
Width	11.4 mm		

General data

Colour	black	Free from halogens	false
Insulating material	PC glass-fibre reinforced (UL-listed and railway-certified)	Low smoke acc. DIN EN 45545-2	Yes
Material	Polyamide, glass fibre-reinforced	Number of poles	2
Series	ConCept module	Type	Pin
Type of connection	Hose connection (pneumatic)	UL 94 flammability rating	V-0

Version

Material	Polyamide, glass fibre-reinforced	Type of connection	Hose connection (pneumatic)
----------	-----------------------------------	--------------------	-----------------------------

Classifications

ETIM 6.0	EC002943	ETIM 7.0	EC002943
ETIM 8.0	EC002943	ETIM 9.0	EC002943
ETIM 10.0	EC002943	ECLASS 9.0	27-44-02-92
ECLASS 9.1	27-44-01-92	ECLASS 10.0	27-44-02-92
ECLASS 11.0	27-44-02-92	ECLASS 12.0	27-44-02-92
ECLASS 13.0	27-44-02-92	ECLASS 14.0	27-44-02-92
ECLASS 15.0	27-44-02-92		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	89f35219-185b-451d-94d0-702fad8bee24

Creation date May 8, 2025 11:05:59 PM CEST

HDC-CM-2SPN4.0

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN