

**WSMC 21-25****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

WSM is a complete marking system for cables, conductors, pipes and components - it offers permanent labelling in environments which no other marker is able to withstand. This product line consists of labelling plates, carriers and stainless steel cable ties – available individually or complete in the WSM Set and Service Box.

**Advantages:**

- Sturdy embossed characters for maximum legibility
- Resistant to heat, cold, corrosion, acids, chemicals, fire, etc.
- Individual and multi-character markings, can also be combined
- Quick installation
- Ideal for outdoor applications
- Easy attachment with cable ties

**General ordering data**

|            |                                                                           |
|------------|---------------------------------------------------------------------------|
| Version    | Stainless steel markers, Conductor and cable markers, 131 x 10 mm, silver |
| Order No.  | <a href="#">1912150000</a>                                                |
| Type       | WSMC 21-25                                                                |
| GTIN (EAN) | 4032248541195                                                             |
| Qty.       | 1 pc(s).                                                                  |

## WSMC 21-25

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Depth      | 0.5 mm | Depth (inches)  | 0.02 inch  |
| Height     | 131 mm | Height (inches) | 5.157 inch |
| Width      | 10 mm  | Width (inches)  | 0.394 inch |
| Net weight | 3 g    |                 |            |

## Temperatures

|                             |        |
|-----------------------------|--------|
| Operating temperature range | 500 °C |
|-----------------------------|--------|

## General data

|                                      |                                                |                |
|--------------------------------------|------------------------------------------------|----------------|
| Colour                               | silver                                         |                |
| Material                             | Stainless steel 1.4404                         |                |
| Number of characters                 | 25                                             |                |
| Number of markers per combination    | 1 Component part = Conductor and cable markers |                |
| Number of markers per packaging unit | Form of supply                                 | Component part |
| Number per sheet                     | 1                                              |                |
| Operating temperature range          | 500 °C                                         |                |
| Operating temperature range, max.    | 500 °C                                         |                |
| Orientation of print                 | horizontal                                     |                |
| Printed characters                   | Mixed characters                               |                |
| Type of printing                     | To customer specification                      |                |
| Width                                | 10 mm                                          |                |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 9.0  | 27-40-04-01 |
| ECLASS 9.1  | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |
| ECLASS 13.0 | 27-28-11-02 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|            |                                          |
|------------|------------------------------------------|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|------------------------------------------|