

HDC CM BUS SV M4 CT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The ConCept-CSB module is a double module and takes up two slots in the ConCept module frame. The ConCept-CSB module consists of a module carrier that is capable of holding two contact carriers. The contact carrier is manufactured with a die-cast zinc alloy which provides it with excellent shielding capabilities. The crimp contacts are insulated from the contact carrier and mounted in a plastic insert. A variety of pole counts – 1, 4 and 8 poles – are available to ensure compatibility with a wide range of applications.

General ordering data

Version	Heavy-duty connectors, HDC insert, ConCept module
Order No.	1983790000
Type	HDC CM BUS SV M4 CT
GTIN (EAN)	4032248688937
Qty.	1 pc(s).

HDC CM BUS SV M4 CT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	18.5 mm	Depth (inches)	0.728 inch
Height	47.5 mm	Height (inches)	1.87 inch
Width	13.5 mm	Width (inches)	0.531 inch
Length	18.5 mm	Length (inches)	0.728 inch
Net weight	24.5 g		

Temperatures

Limit temperature	-40 °C ... 70 °C
-------------------	------------------

ConCept Pneumatic module

Colour	Silver grey	UL 94 flammability rating	V-0
--------	-------------	---------------------------	-----

Dimensions

Height of plug	47.5 mm	Total length base	18.5 mm
Width	13.5 mm		

General data

Colour	Silver grey	Free from halogens	false
Low smoke acc. DIN EN 45545-2	Yes	Material	Zinc, Polycarbonate
Number of poles	4	Plugging cycles	≥ 500
Rated current (DIN EN 61984)	10 A	Rated impulse voltage (DIN EN 61984)	0.8 kV
Rated voltage (DIN EN 61984)	50 V	Series	ConCept module
Type	Pin	Type of connection	Crimp connection
UL 94 flammability rating	V-0	Volume resistance	≤4 mΩ

Version

Material	Zinc, Polycarbonate	Stripping length, rated connection	8 mm
Type of connection	Crimp connection	Volume resistance	≤4 mΩ

Classifications

ETIM 6.0	EC002312	ETIM 7.0	EC002312
ETIM 8.0	EC000438	ETIM 9.0	EC000438
ETIM 10.0	EC000438	ECLASS 9.0	27-44-02-92
ECLASS 9.1	27-44-02-18	ECLASS 10.0	27-44-02-92
ECLASS 11.0	27-44-02-92	ECLASS 12.0	27-44-02-92
ECLASS 13.0	27-44-02-92	ECLASS 14.0	27-44-02-92
ECLASS 15.0	27-44-02-92		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	1609748e-c278-4c9b-b3d1-e6215d2988cd

HDC CM BUS SV M4 CT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Approvals**

Approvals



Approvals MAMID	https://mdcop.weidmueller.com/mediadelivery/rendition/900_319226/-T1z1mm-S800/ https://mdcop.weidmueller.com/mediadelivery/rendition/900_319230/-T1z1mm-S800/ https://mdcop.weidmueller.com/mediadelivery/rendition/900_319234/-T1z1mm-S800/
-----------------	---

ROHS	Conform
------	---------

UL File Number Search	UL Website
-----------------------	------------

Certificate No. (cULus)	E92202
-------------------------	--------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN