

ZE PTSC 3X27 PT6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Extensive range of accessories for the FieldPower® boxes.

Cable seals, terminal rails, locking elements and much more.

General ordering data

Version	Strain relief, Polyamide 66, Strain relief for energy bus of PT6 contact element, For 15 - 17 mm cable diameter
Order No.	2370760000
Type	ZE PTSC 3X27 PT6
GTIN (EAN)	4032248991075
Qty.	100 pc(s).

ZE PTSC 3X27 PT6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	0.05 g
------------	--------

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...55 °C
---------------------	----------------	-----------------------	----------------

General data

Material	Polyamide 66	Silicone	No
Colour	orange	Type of mounting	Screw mounting
Mounting position, installation notice	Strain relief for energy bus of PT6 contact element, For 15 - 17 mm cable diameter	Installation advice	Screws included

Classifications

ETIM 6.0	EC002939	ETIM 7.0	EC002939
ETIM 8.0	EC002939	ETIM 9.0	EC002939
ETIM 10.0	EC002939	ECLASS 9.0	27-40-08-45
ECLASS 9.1	27-06-92-90	ECLASS 10.0	27-40-08-45
ECLASS 11.0	27-40-08-45	ECLASS 12.0	27-40-08-45
ECLASS 13.0	27-40-08-45	ECLASS 14.0	27-40-08-45
ECLASS 15.0	27-40-08-45		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Important note

Product information	Strain relief Power Bus
---------------------	-------------------------

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	Manufacturer's Declaration FieldPower® BOX, BOX FUSE and Terminal variants
Catalogues	Catalogues in PDF-format

ZE PTSC 3X27 PT6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****E6.3 bits - Pozidriv / Supadriv**

1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection
Crosshead bits Pozidriv PZ/DIN 5262, 1/4" drive, E 6.3
DIN 3126

General ordering data

Type	BIT E6,3 PZ2X70	Version
Order No.	2748970000	Screwdriver insert, Blade width (B): 2 mm, Blade length: 70 mm,
GTIN (EAN)	4050118895162	Blade thickness (A): 2 mm, Blade size, crosshead: 2
Qty.	5 pc(s).	

DMS PRO

Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

General ordering data

Type	DMS PRO	Version
Order No.	1479120000	Mounting tool
GTIN (EAN)	4050118287011	
Qty.	1 pc(s).	

ZE PTSC 3X27 PT6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Crosshead screwdriver Pozidriv**

Crosshead screwdriver, Pozidriv, SDK PZ DIN 5262, ISO 8764/2-PZ, output to ISO 8764/1-PZ, ChromTop tip, SoftFinish grip

General ordering data

Type	SDK PZ2 X 100	Version
Order No.	2749450000	Screwdriver, Blade width (B): 2 mm, 100 mm, Blade thickness (A):
GTIN (EAN)	4050118895674	
Qty.	1 pc(s).	