

VT M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- Reacts from a distance of 4 mm
- for testing operation of solenoid valves, relays, coils and contactors
- all magnetic fields can be tested
- Visual and acoustic indication
- including a flashlight function

General ordering data

Version	Testing tools, Non-contact magnetic field tester
Order No.	2436680000
Type	VT M
GTIN (EAN)	4050118450019
Qty.	1 pc(s).

VT M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Length	155 mm	Length (inches)	6.102 inch
Net weight	55.7 g		

Technical data

Description of article	Non-contact magnetic field tester
------------------------	-----------------------------------

Measuring and testing devices

Battery type	1.5 V type AAA battery	Display	Visual & acoustic
Protection degree	IP65	Tested and approved according to	DIN EN 61010-1, DIN EN 61326

Classifications

ETIM 6.0	EC000494	ETIM 7.0	EC000494
ETIM 8.0	EC000494	ETIM 9.0	EC000494
ETIM 10.0	EC000494	ECLASS 9.0	27-20-03-08
ECLASS 9.1	27-20-03-08	ECLASS 10.0	27-20-03-08
ECLASS 11.0	27-20-03-08	ECLASS 12.0	27-20-03-08
ECLASS 13.0	27-20-03-08	ECLASS 14.0	27-20-03-08
ECLASS 15.0	27-20-03-08		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	b05b5122-6117-4cb0-b28c-df32f921fa36

Approvals

Approvals



Approvals MAMID	https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/
ROHS	Conform

Downloads

User Documentation	Manual
Catalogues	Catalogues in PDF-format