

CMA-CTM-7-32-1A-0.2VA-1**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

similar to the product

The CMA-CTM 7 series mini current transformer is an inductive current transformer designed according to the transformer principle for circular primary conductors.

The CMA-CTM 7 series current transformers are maintenance-free and is designed for measuring primary currents in the range 32 A to 64 A. This is converted into a current up to 1 A on the secondary side.

With its small dimensions, it perfectly suits applications in a 3-phase circuit breaker with a phase separation of 17.5 mm.

General ordering data

Version	Primary current: 32 A, Secondary current max.: 1 A, Load: 0.2 VA, Tolerance class: 1, closed current transformer
Order No.	2525150000
Type	CMA-CTM-7-32-1A-0.2VA-1
GTIN (EAN)	4050118536515
Qty.	1 pc(s).
Manufacturer	MBS AG

CMA-CTM-7-32-1A-0.2VA-1

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	19 mm	Depth (inches)	0.748 inch
Height	46.5 mm	Height (inches)	1.831 inch
Width	27.5 mm	Width (inches)	1.083 inch
Net weight	64 g		

Temperatures

Storage temperature	-25 °C...70 °C	Operating temperature	-5 °C...50 °C
---------------------	----------------	-----------------------	---------------

Dimensions of live conductors

Type of conductor	Insulated conductor only	Round conductor	7.6 mm
Installation location	Indoor use		

Electrical attributes

Load	0.2 VA	Primary current	32 A
Secondary current	0...1 A	Tolerance class	1

Technical properties

Insulation class	E	Nominal frequency	50 Hz
Thermal rated continuous current $I_{\text{thermal}} 1.0 \times I_{\text{rated}}$			

Insulation coordination

Standard	IEC 61869-1: 2007, IEC 61869-2: 2012, IEC 61010-1	Tolerance class	1
----------	---	-----------------	---

Classifications

ETIM 6.0	EC002048	ETIM 7.0	EC002048
ETIM 8.0	EC002048	ETIM 9.0	EC002048
ETIM 10.0	EC002048	ECLASS 9.0	27-21-09-02
ECLASS 9.1	27-21-09-02	ECLASS 10.0	27-21-09-02
ECLASS 11.0	27-21-09-02	ECLASS 12.0	27-21-09-02
ECLASS 13.0	27-21-09-02	ECLASS 14.0	27-21-09-02
ECLASS 15.0	27-21-09-02		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

CMA-CTM-7-32-1A-0.2VA-1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of Conformity	UL- certificate Declaration of Conformity UKCA Declaration of Conformity
Engineering Data	CAD data – STEP
User Documentation	Device description – Betriebsanleitung deutsch
Catalogues	Catalogues in PDF-format

CMA-CTM-7-32-1A-0.2VA-1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

