

**CD-SE 40/2****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

**General ordering data**

|                 |                                                                |
|-----------------|----------------------------------------------------------------|
| Version         | Cable duct separator, 40 mm x                                  |
| Order No.       | <a href="#">2553950000</a>                                     |
| Type            | CD-SE 40/2                                                     |
| GTIN (EAN)      | 4050118564082                                                  |
| Qty.            | 30 pc(s).                                                      |
| Delivery status | <b>This article will no longer be available in the future.</b> |
| Available until | 2025-12-31                                                     |

**CD-SE 40/2****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Height     | 40 mm    | Height (inches) | 1.575 inch |
| Length     | 1,000 mm | Length (inches) | 39.37 inch |
| Net weight | 210 g    |                 |            |

**Temperatures**

|                             |            |
|-----------------------------|------------|
| Operating temperature range | -5...60 °C |
|-----------------------------|------------|

**General information**

|                           |      |                             |            |
|---------------------------|------|-----------------------------|------------|
| Colour                    | grey | Material                    | PVC        |
| Non-tracking              | Yes  | Operating temperature range | -5...60 °C |
| UL 94 flammability rating | V-0  | Version                     | 2-walled   |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001015    | ETIM 7.0    | EC001015    |
| ETIM 8.0    | EC001015    | ETIM 9.0    | EC001015    |
| ETIM 10.0   | EC001015    | ECLASS 9.1  | 27-40-07-52 |
| ECLASS 10.0 | 27-40-07-52 | ECLASS 11.0 | 27-40-07-52 |
| ECLASS 12.0 | 27-40-07-52 | ECLASS 13.0 | 27-40-07-52 |
| ECLASS 14.0 | 27-40-07-52 | ECLASS 15.0 | 27-40-07-52 |

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|            |                                          |
|------------|------------------------------------------|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|------------------------------------------|