

CD-RET 40**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

General ordering data

Version	Cable duct binder, 2.8 mm x 46 mm
Order No.	2554020000
Type	CD-RET 40
GTIN (EAN)	4050118564150
Qty.	500 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2025-12-31

CD-RET 40**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	15 mm	Depth (inches)	0.591 inch
Height	2.8 mm	Height (inches)	0.11 inch
Width	46 mm	Width (inches)	1.811 inch
Net weight	1.848 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

General information

Channel width	40	Colour	yellow
Material	Polyamide 6 (PA 6)	Non-tracking	Yes
Operating temperature range	-40...100 °C	UL 94 flammability rating	HB
Usage	For 40 mm wiring ducts		

Classifications

ETIM 6.0	EC001018	ETIM 7.0	EC001018
ETIM 8.0	EC001018	ETIM 9.0	EC001018
ETIM 10.0	EC001018	ECLASS 9.0	27-40-07-65
ECLASS 9.1	27-40-07-65	ECLASS 10.0	27-40-07-65
ECLASS 11.0	27-40-07-65	ECLASS 12.0	27-40-07-65
ECLASS 13.0	27-40-07-65	ECLASS 14.0	27-40-07-65
ECLASS 15.0	27-40-07-65		

Approvals

ROHS	Conform
------	---------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Downloads

Catalogues	Catalogues in PDF-format
------------	--