

FF-FIMT 3X 55**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The filter fans combine a safe and profitable cabinet cooling due to their low energy consumption by maximum air flow. The fluted filter mat of the IP 55 version extends the service life by up to 300% in comparison to conventional filter mats.

General ordering data

Version	Filter mat, IP55, white
Order No.	2556730000
Type	FF-FIMT 3X 55
GTIN (EAN)	4050118567359
Qty.	5 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2025-12-31

FF-FIMT 3X 55

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	156 mm	Height (inches)	6.142 inch
Width	166 mm	Width (inches)	6.535 inch
Net weight	18.2 g		

Temperatures

Operating temperature range	-40...55 °C
-----------------------------	-------------

General data

Colour	white	Filter class	G 4
Operating temperature range	-40...55 °C	Protection class (UL)	Type 12
Type of mounting	Snap-on	With filter	Yes

Classifications

ETIM 6.0	EC002513	ETIM 7.0	EC002513
ETIM 8.0	EC002513	ETIM 9.0	EC002513
ETIM 10.0	EC002513	ECLASS 9.1	27-18-07-06
ECLASS 10.0	27-18-07-06	ECLASS 11.0	27-18-07-06
ECLASS 12.0	27-18-07-06	ECLASS 13.0	27-18-07-06
ECLASS 14.0	27-18-07-06	ECLASS 15.0	27-18-07-06

Approvals

ROHS	Conform
------	---------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Downloads

User Documentation	Operating instructions
Catalogues	Catalogues in PDF-format