

HDC 64D SBU 2PG29G N**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Version	HDC enclosures, Size: 8, Protection degree: IP65, in plugged condition, Base housing, Side-locking clamp on lower side, high, Size of cable entries: M 32
Order No.	2560790000
Type	HDC 64D SBU 2PG29G N
GTIN (EAN)	4050118894103
Qty.	1 pc(s).

HDC 64D SBU 2PG29G N**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Height	84 mm	Height (inches)	3.307 inch
Width	57.5 mm	Width (inches)	2.264 inch
Length	163 mm	Length (inches)	6.417 inch
Mounting dimension - height	45 mm	Mounting dimension - width	132 mm
Net weight	491 g		

Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

Dimensions

Cable entry	w. thread	Height of base B1	5 mm
Height of housing B	84 mm	Hole pitch length A2	132 mm
Total length housing	120 mm	Width base C1	57.5 mm
Width housing C	43 mm		

General data

EMC housings	No	Housing main material	diecast aluminium
Material of locking element	Polyamide, Stainless steel, rust-proof	Protection degree	IP65, in plugged condition
Surface finish	Powder coating		

Version

BG	8	Cable entry	w. thread
Clamp version	Side-locking clamp	Colour (RAL)	RAL 7035
Design	high	Design of housing	Base housing
Design of locking system	Side-locking clamp on lower side	Internal thread	M 32
Number of cable entry on top	0	Number of cable entry sideways	2
Sealing	NBR	Size	8
Size of cable entries	M 32	Suitable for ModuPlug®	Yes
Top part/bottom part/lid	lower part	Type	Base housing

Classifications

ETIM 6.0	EC000437	ETIM 7.0	EC000437
ETIM 8.0	EC000437	ETIM 9.0	EC000437
ETIM 10.0	EC000437	ECLASS 9.0	27-44-02-02
ECLASS 9.1	27-44-02-02	ECLASS 10.0	27-44-02-02
ECLASS 11.0	27-44-02-02	ECLASS 12.0	27-44-02-02
ECLASS 13.0	27-44-02-02	ECLASS 14.0	27-44-02-02
ECLASS 15.0	27-44-02-02		

HDC 64D SBU 2PG29G N**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Approvals**

Approvals

Approvals MAMID https://mdcop.weidmueller.com/mediadelivery/rendition/900_319230/-T1z1mm-S800/

ROHS Conform

UL File Number Search UL Website

Certificate No. (cURus) E92202

Substance	Acetone
Chemical resistance	Conditionally resistant
Substance	Drilling oil
Chemical resistance	Resistant
Substance	Diesel
Chemical resistance	Resistant
Substance	Ethyl alcohol
Chemical resistance	Resistant
Substance	Transmission oil
Chemical resistance	Resistant
Substance	Hydraulic oil
Chemical resistance	Resistant
Substance	Coolant
Chemical resistance	Resistant
Substance	Petroleum benzine
Chemical resistance	Resistant
Substance	Sweat
Chemical resistance	Resistant
Substance	Premium gasoline
Chemical resistance	Conditionally resistant
Substance	Water
Chemical resistance	Resistant
Substance	UV
Chemical resistance	Unstable
Substance	Ozone
Chemical resistance	Unstable

HDC 64D SBU 2PG29G N**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%
Chemical resistance	de.myview.objectmodel.impl.BlockImpl@4d5ebba6 de.myview.objectmodel.impl.BlockImpl@da23853 de.myview.objectmodel.impl.BlockImpl@53c5f445 de.myview.objectmodel.impl.BlockImpl@57a8afc4 de.myview.objectmodel.impl.BlockImpl@6f93ad1c de.myview.objectmodel.impl.BlockImpl@736f701d de.myview.objectmodel.impl.BlockImpl@ff4c5e9 de.myview.objectmodel.impl.BlockImpl@1d308d5c de.myview.objectmodel.impl.BlockImpl@6fb928ab de.myview.objectmodel.impl.BlockImpl@675e42d9 de.myview.objectmodel.impl.BlockImpl@4eac0856 de.myview.objectmodel.impl.BlockImpl@57ef26b2 de.myview.objectmodel.impl.BlockImpl@7135b094

Downloads

Engineering Data	CAD data – STEP
Product Change Notification	20220214 Technical change to HDC housings 20220214 Technische Änderung bei HDC-Gehäusen
Catalogues	Catalogues in PDF-format

HDC 64D SBU 2PG29G N

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

XXL plug housing, cable entry on top



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Type	HDC 64D TOBU 1M50G	Version
Order No.	1111140000	HDC enclosures, Size: 8, Protection degree: IP65, in plugged condition, Cable entry from top, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: M 50
GTIN (EAN)	4032248964413	
Qty.	1 pc(s).	

Hood, Cable Entry at top



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Type	HDC 64D TOBU 2M32G	Version
Order No.	1009710000	HDC enclosures, Size: 8, Protection degree: IP65, in plugged condition, Cable entry from top, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: M 32
GTIN (EAN)	4032248771394	
Qty.	1 pc(s).	
Type	HDC 24B TOBU 1M25G	Version
Order No.	1787820000	HDC enclosures, Size: 8, Protection degree: IP65, in plugged condition, Cable entry from top, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: M 25
GTIN (EAN)	4032248205264	
Qty.	1 pc(s).	

HDC 64D SBU 2PG29G N

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type	HDC 24B TOBU 1M40G	Version
Order No.	1902980000	HDC enclosures, Size: 8, Protection degree: IP65, in plugged
GTIN (EAN)	4032248585274	condition, Cable entry from top, Plug housing, Side-locking clamp on
Qty.	1 pc(s).	lower side, Standard, Size of cable entries: M 40
Type	HDC 64D TOBU 1M32G	Version
Order No.	1786830000	HDC enclosures, Size: 8, Protection degree: IP65, in plugged
GTIN (EAN)	4032248204076	condition, Cable entry from top, Plug housing, Side-locking clamp on
Qty.	1 pc(s).	lower side, high, Size of cable entries: M 32
Type	HDC 24B TOBU 1PG21G	Version
Order No.	1661370000	HDC enclosures, Size: 8, Protection degree: IP65, in plugged
GTIN (EAN)	4008190417925	condition, Cable entry from top, Plug housing, Side-locking clamp on
Qty.	1 pc(s).	lower side, Standard, Size of cable entries: PG 21
Type	HDC 64D TOBU 1PG29G	Version
Order No.	1661460000	HDC enclosures, Size: 8, Protection degree: IP65, in plugged
GTIN (EAN)	4008190418014	condition, Cable entry from top, Plug housing, Side-locking clamp on
Qty.	1 pc(s).	lower side, high, Size of cable entries: PG 29
Type	HDC 64D TOBU 1M40G	Version
Order No.	1045560000	HDC enclosures, Size: 8, Protection degree: IP65, in plugged
GTIN (EAN)	4032248780532	condition, Cable entry from top, Plug housing, Side-locking clamp on
Qty.	1 pc(s).	lower side, high, Size of cable entries: M 40
Type	HDC 24B TOBU 1PG29G	Version
Order No.	1661380000	HDC enclosures, Size: 8, Protection degree: IP65, in plugged
GTIN (EAN)	4008190417932	condition, Cable entry from top, Plug housing, Side-locking clamp on
Qty.	1 pc(s).	lower side, Standard, Size of cable entries: PG 29
Type	HDC 24B TOBU 1M32G	Version
Order No.	1787810000	HDC enclosures, Size: 8, Protection degree: IP65, in plugged
GTIN (EAN)	4032248205257	condition, Cable entry from top, Plug housing, Side-locking clamp on
Qty.	1 pc(s).	lower side, Standard, Size of cable entries: M 32
Type	HDC 64D TOBU 1PG21G	Version
Order No.	1661440000	HDC enclosures, Size: 8, Protection degree: IP65, in plugged
GTIN (EAN)	4008190417994	condition, Cable entry from top, Plug housing, Side-locking clamp on
Qty.	1 pc(s).	lower side, high, Size of cable entries: PG 21

HDC 64D SBU 2PG29G N

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Hood, Cable Entry sideways



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Type	HDC 24B TSBU 1M25G	Version
Order No.	1787760000	HDC enclosures, Size: 8, Protection degree: IP65, in plugged condition, Cable entry from side, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: M 25
GTIN (EAN)	4032248205103	
Qty.	1 pc(s).	
Type	HDC 64D TSBU 1PG21G	Version
Order No.	1661300000	HDC enclosures, Size: 8, Protection degree: IP65, in plugged condition, Cable entry from side, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: PG 21
GTIN (EAN)	4008190417857	
Qty.	1 pc(s).	
Type	HDC 64D TSBU 1M32G	Version
Order No.	1786770000	HDC enclosures, Size: 8, Protection degree: IP65, in plugged condition, Cable entry from side, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: M 32
GTIN (EAN)	4032248204014	
Qty.	1 pc(s).	
Type	HDC 24B TSBU 1PG29G	Version
Order No.	1661240000	HDC enclosures, Size: 8, Protection degree: IP65, in plugged condition, Cable entry from side, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: PG 29
GTIN (EAN)	4008190417796	
Qty.	1 pc(s).	
Type	HDC 64D TSBU 1M40G	Version
Order No.	1809630000	HDC enclosures, Size: 8, Protection degree: IP65, in plugged condition, Cable entry from side, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: M 40
GTIN (EAN)	4032248284986	
Qty.	1 pc(s).	
Type	HDC 64D TSBU 1PG29G	Version
Order No.	1661320000	HDC enclosures, Size: 8, Protection degree: IP65, in plugged condition, Cable entry from side, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: PG 29
GTIN (EAN)	4008190417871	
Qty.	1 pc(s).	
Type	HDC 64D TSBU 1M25G	Version
Order No.	1786780000	HDC enclosures, Size: 8, Protection degree: IP65, in plugged condition, Cable entry from side, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: M 25
GTIN (EAN)	4032248204021	
Qty.	1 pc(s).	
Type	HDC 24B TSBU 1M40G	Version
Order No.	1902480000	HDC enclosures, Size: 8, Protection degree: IP65, in plugged condition, Cable entry from side, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: M 40
GTIN (EAN)	4032248592944	
Qty.	1 pc(s).	

HDC 64D SBU 2PG29G N

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type	HDC 24B TSB 1M32G	Version
Order No.	1787750000	HDC enclosures, Size: 8, Protection degree: IP65, in plugged
GTIN (EAN)	4032248205097	condition, Cable entry from side, Plug housing, Side-locking clamp on
Qty.	1 pc(s).	lower side, Standard, Size of cable entries: M 32
Type	HDC 24B TSB 1PG21G	Version
Order No.	1661230000	HDC enclosures, Size: 8, Protection degree: IP65, in plugged
GTIN (EAN)	4008190417789	condition, Cable entry from side, Plug housing, Side-locking clamp on
Qty.	1 pc(s).	lower side, Standard, Size of cable entries: PG 21

Cover



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Type	HDC 24B DODQ 4B0	Version
Order No.	1665630000	HDC enclosures, Size: 8, Protection degree: IP65, in plugged
GTIN (EAN)	4008190422653	condition, Cover for lower part of housing, Side-locking clamp on
Qty.	1 pc(s).	lower side, Standard

HDC 64D SBU 2PG29G N**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****XXL plug housing, cable entry sideways**

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Type	HDC 64D TSB 1M50G	Version
Order No.	1111130000	HDC enclosures, Size: 8, Protection degree: IP65, in plugged
GTIN (EAN)	4032248967711	condition, Cable entry from side, Plug housing, Side-locking clamp on
Qty.	1 pc(s).	lower side, high, Size of cable entries: M 50