

CD-LID 125 DKG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

General ordering data

Version	Cable duct cover, 125 mm
Order No.	2588980000
Type	CD-LID 125 DKG
GTIN (EAN)	4050118602449
Qty.	2 m
Delivery status	Discontinued

CD-LID 125 DKG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Width	125 mm	Width (inches)	4.921 inch
Length	2,000 mm	Length (inches)	78.74 inch
Net weight	265 g		

Temperatures

Operating temperature range	-25...120 °C
-----------------------------	--------------

General information

Colour	dark grey	Flexible wiring duct	No
Halogen	No	Lid	Yes
Material	PPE	Non-tracking	Yes
Operating temperature range	-25...120 °C	Type of mounting	Snap-on
UL 94 flammability rating	V-0		

Classifications

ETIM 6.0	EC000727	ETIM 7.0	EC000727
ETIM 8.0	EC000727	ETIM 9.0	EC000727
ETIM 10.0	EC000727	ECLASS 9.1	27-40-07-76
ECLASS 10.0	27-40-07-76	ECLASS 11.0	27-40-07-76
ECLASS 12.0	27-40-07-76	ECLASS 13.0	27-40-07-76
ECLASS 14.0	27-40-07-76	ECLASS 15.0	27-40-07-76

Approvals

ROHS	Conform
------	---------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Downloads

Catalogues	Catalogues in PDF-format
------------	--