

FP ENC DR07 230 3B**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Extensive range of accessories for the FieldPower® boxes.

Cable seals, terminal rails, locking elements and much more.

General ordering data

Version	Field Power® terminal rail, Steel, galvanized, 230 mm, for base part
Order No.	2633460000
Type	FP ENC DR07 230 3B
GTIN (EAN)	4050118664409
Qty.	5 pc(s).

FP ENC DR07 230 3B

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	7.5 mm	Depth (inches)	0.295 inch
Height	35 mm	Height (inches)	1.378 inch
Width	230 mm	Width (inches)	9.055 inch
Net weight	8.8 g		

Temperatures

Operating temperature	-40 °C...85 °C
-----------------------	----------------

General specifications

Insulating material	Steel	Material	Steel, galvanized
Colour	silver, black		

General data

Material	Steel, galvanized	Insulating material	Steel
Colour	silver, black	Type of mounting	Plugged
Mounting position, installation notice	for base part	Version	without slot

Classifications

ETIM 6.0	EC001285	ETIM 7.0	EC001285
ETIM 8.0	EC001285	ETIM 9.0	EC001285
ETIM 10.0	EC001285	ECLASS 9.0	27-40-06-02
ECLASS 9.1	27-40-06-02	ECLASS 10.0	27-40-06-02
ECLASS 11.0	27-40-06-02	ECLASS 12.0	27-40-06-02
ECLASS 13.0	27-40-06-02	ECLASS 14.0	27-40-06-02
ECLASS 15.0	27-40-06-02		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	Manufacturer's Declaration FieldPower® Enclosure parts
Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

FP ENC DR07 230 3B

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

